


760026815 | R-096-DS-6F-FMUSL

Riser Distribution Cable, 96 fiber multi-unit with 12 fiber subunits

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	OptiSPEED®, 62.5 µm multimode fiber
Total Fiber Quantity	96
Fiber Type	OptiSPEED®, 62.5 µm multimode fiber
Fiber Type, quantity	96
Fibers Per Subunit, quantity	12
Jacket Color	Slate

Dimensions

Buffer Tube/Subunit Diameter	6.00 mm   0.24 in
Cable Weight	337.0 lb/kft   502.0 kg/km
Diameter Over Jacket	23.70 mm   0.93 in
Subunit, quantity	8

Physical Specifications

Minimum Bend Radius, loaded	35.6 cm   14.0 in
Minimum Bend Radius, unloaded	23.7 cm   9.3 in
Tensile Load, long term, maximum	1335 N   300 lbf

760026815 | R-096-DS-6F-FMUSL

Tensile Load, short term, maximum 1000 lbf | 4450 N  
Vertical Rise, maximum 271.0 m | 889.1 ft

## Flame Test Specifications

Flame Test Listing	NEC OFNR (ETL) and c(ETL)
Flame Test Method	UL 1666

## Environmental Specifications

Environmental Space	Riser
Installation Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## Mechanical Test Specifications

Compression	10 N/mm   57 lb/in
Compression Test Method	FOTP-41   IEC 60794-1-2, Section 7
Flex	100 cycles
Flex Test Method	FOTP-104   IEC 60794-1-2, Section 10
Impact	4.34 ft lb   5.88 N-m
Impact Test Method	FOTP-25   IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1-2, Section 11

## Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-28   IEC 60794-1-2, Section 28
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1-2, Section 22

## Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596-2001   Telcordia GR-409-CORE Issue 2
-------------------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

---

CS-6F-TB (Product Component—not orderable) — OptiSPEED® OM1 Multimode Fiber