



760082537 | RK4P52-29A

29 in (737 mm) D x 8 ft (2438 mm) H - 19 in (482.6 mm) Al Equipment Rack (52U) 12-24 Tapped Rails, Black

Dimensions

Channel Width	3.0 in
Depth	1041.4 mm 41.0 in
Dimensional Standards	EIA-310-E
Height	2438.4 mm 96.0 in
Weight	41.28 kg 91.00 lb
Width	518.2 mm 20.4 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Product Type	4 post rack
Rack Units	52
Color	Black
Finish	Powder-coated, textured
Includes	Base pan Forty #12-24 x 1/2 in mounting screws Four vertical rack rails Instruction sheet Twelve 3/8 in split lock washers Twelve 3/8 -16 hex nuts Twelve 3/8-16 UNC x 1 in hex head bolts Two extruded base angles Two extruded top angles Upper plate support
Package, quantity	1
Packaging Type	Flat packed
Rack Type	EIA 19 in

Mechanical Specifications

Rail Mounting Hole	#12-24
Material Type	Aluminum
Static Load Rating	907.2 kg 2000.0 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMScope®

760082537 | RK4P52-29A

