



760090167 | RK12-52S

12 in (305 mm) Channel x 8ft (2438 mm) H - 19 in (482.6 mm) Steel Equipment Rack (52U) 3/8 Sq Punch, Black

Dimensions

| | |
|-----------------------|---------------------|
| Channel Width | 12.0 in |
| Depth | 609.6 mm 24.0 in |
| Dimensional Standards | EIA-310-E |
| Height | 2438.4 mm 96.0 in |
| Weight | 28.12 kg 62.00 lb |
| Width | 518.2 mm 20.4 in |

Environmental Specifications

| | |
|-----------------|----------|
| Safety Standard | cUL UL |
|-----------------|----------|

General Specifications

| | |
|-------------------|---|
| Product Type | 2 post rack |
| Rack Units | 52 |
| Color | Black |
| Finish | Powder-coated, textured |
| Includes | Forty #12-24 x 1/2 in mounting screws Forty M6 cage nuts Instruction sheet Twelve 3/8 in split lock washers Twelve 3/8 -16 hex nuts Twelve 3/8 -16 UNC x 1 in hex head bolts Two extruded base angles Two extruded top angles Two vertical rack rails |
| Package, quantity | 1 |
| Packaging Type | Flat packed |
| Rack Type | EIA 19 in |

Mechanical Specifications

| | |
|--------------------|----------------------|
| Rail Mounting Hole | 3/8 in |
| Material Type | Steel |
| Static Load Rating | 453.6 kg 1000.0 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|--|
| RoHS 2002/95/EC | Compliant |
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

