

760095745 | CW26-PSS-24

Wall Mount Cabinet, 48 in (1219 mm) H (26U), Plexiglass Door, Solid Sides, Solid Top/Bottom, 24 in (610 mm) Deep, 12-24 Tapped Rails

Dimensions

Height	1219.2 mm 48.0 in
Depth	609.6 mm 24.0 in
Dimensional Standards	EIA-310-E
Weight	34.02 kg 75.00 lb
Width	584.2 mm 23.0 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Rack Units	26
Color	Black
Finish	Powder-coated, hammertone
Includes	Instruction sheet Twenty #12 -24 x 1/2 in mounting screws Wall mount cabinet
Package, quantity	1
Packaging Type	Assembled

Mechanical Specifications

Door Material, front	Plexiglass
Side Panel Vent	Solid
Top Panel Vent	Solid
Static Load Rating	56.7 kg 125.0 lb
Bottom Panel	Included
Bottom Panel Vent	Solid
Cable Entry, bottom	Two 1 in diameter openings Two 3 in diameter openings
Cable Entry, top	Two openings of 1 in diameter Two 3 in diameter openings
Door Type, front	Single
Door Vent, front	Solid
Material Type	Steel
Side Panels	Included
Top Panel	Included

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

