

760096032 | CW12-PVF-24HD

**Wall Mount Cabinet, Heavy Duty, 24 in (610 mm) H (12U), Plexiglass Door, Vented Sides, 2 Fans, 24 in (610 mm) Deep, 12-24 Tapped Rails**

## Dimensions

Height	609.6 mm   24.0 in
Depth	609.6 mm   24.0 in
Dimensional Standards	EIA-310-E
Weight	34.02 kg   75.00 lb
Width	558.8 mm   22.0 in

## Environmental Specifications

Safety Standard	cUL   UL
-----------------	----------

## General Specifications

Rack Units	12
Color	Black
Finish	Powder-coated, hammertone
Includes	Instruction sheet   Twenty #12 -24 x 1/2 in mounting screws   Two 115 V fans   Wall mount cabinet
Package, quantity	1
Packaging Type	Assembled

## Mechanical Specifications

Door Material, front	Plexiglass
Side Panel Vent	Vented
Top Panel Vent	Vented/Perforated
Static Load Rating	136.1 kg   300.0 lb
Bottom Panel	Included
Bottom Panel Vent	Vented
Cable Entry, bottom	Two 1 in diameter openings   Two 3 in diameter openings
Cable Entry, top	Two openings of 1 in diameter   Two 3 in diameter openings
Door Type, front	Single
Door Vent, front	Solid
Material Type	Steel
Side Panels	Included
Top Panel	Included

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

# Product Specifications

COMMSCOPE®

760096032 | CW12-PVF-24HD

---



## Included Products

---

760096099 | CWFK2-120 — Fan Kit, 2 Fans, 120VAC