




760112540 | R-012-LN-5M-
F12BK/25D/LTS

Light Duty Indoor/Outdoor All-Dielectric Single Jacket Riser Rated Stranded Loose Tube Gel-Free Cable

Representative Image



General Specifications

Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	LazrSPEED® 150, 50 µm multimode fiber
Total Fiber Quantity	12
Fiber Type	LazrSPEED® 150, 50 µm multimode fiber
Fiber Type, quantity	12
Fibers Per Subunit, quantity	12
Jacket Color	Black
Jacket UV Resistance	UV stabilized

Dimensions

Buffer Tube/Subunit Diameter	2.50 mm 0.10 in
Cable Weight	94.0 kg/km 63.0 lb/kft
Diameter Over Jacket	10.40 mm 0.41 in
Filler, quantity	3
Subunit, quantity	1

Physical Specifications

760112540 | R-012-IN-5MF12BK/25D/LTS

Minimum Bend Radius, loaded	15.7 cm		6.2 in
Minimum Bend Radius, unloaded	10.4 cm		4.1 in
Tensile Load, long term, maximum	90 lbf		400 N
Tensile Load, short term, maximum	1335 N		300 lbf
Vertical Rise, maximum	436.0 m		1430.4 ft

Flame Test Specifications

Flame Test Listing	NEC OFNR (ETL) and c(ETL)
Flame Test Method	UL 1666

Environmental Specifications

Environmental Space	Riser
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

Mechanical Test Specifications

Compression	125 lb/in		22 N/mm
Compression Test Method	FOTP-41		IEC 60794-1-2, Section 7
Flex	35 cycles		
Flex Test Method	FOTP-24		IEC 60794-1-2, Section 10
Impact	2.17 ft lb		2.94 N-m
Impact Test Method	FOTP-25		IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads		
Strain Test Method	FOTP-33		IEC 60794-1-2, Section 5
Twist	10 cycles		
Twist Test Method	FOTP-85		IEC 60794-1-2, Section 11
Water Penetration	24 h		
Water Penetration Test Method	FOTP-82		IEC 60794-1-2, Section 24

Environmental Test Specifications

Cable Freeze	-2 °C		28 °F
Cable Freeze Test Method	FOTP-98		
Heat Age	-40 °C to +85 °C	(-40 °F to +185 °F)	
Heat Age Test Method	Not applicable		
Low High Bend	-30 °C to +60 °C	(-22 °F to +140 °F)	
Low High Bend Test Method	FOTP-28		IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C	(-40 °F to +158 °F)	
Temperature Cycle Test Method	FOTP-3		IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-104-696-2001		EN 187105
-------------------------------	--------------------------	--	-----------

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

Product Specifications

COMMSCOPE®

760112540 | R-012-IN-5MF12BK/25D/LTS

RoHS 2002/95/EC
ISO 9001:2008

Compliant
Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5M-LT (Product Component—not orderable) — LazrSPEED® 150 OM2+ Multimode Fiber