



SSH-12-4

SnapStak® Hanger for 1/2 in coaxial cable, quadruple stack capability, includes reinforcement bar

Dimensions

Nominal Size	1/2 in
Compatible Diameter, maximum	16.256 mm 0.640 in
Compatible Diameter, minimum	13.716 mm 0.540 in
Height	41.00 mm 1.61 in
Length	66.00 mm 2.60 in
Width	22.80 mm 0.90 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

General Specifications

Hanger Type	Snap-in hanger
Cables Per Hanger	1
Color	Silver
Material Type	Stainless steel
Maximum Stack Height	4
Package Quantity	10

Mechanical Specifications

Axial Load Capability, minimum with no cable slippage	≥5 times cable weight
Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	3/4 in drilled cable ladder
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Vibration Survival	≥4 hours at resonant frequency

Packed Dimensions

Height	15.2 cm 6.0 in
Length	9.0 cm 3.5 in
Shipping Weight	0.36 kg 0.79 lb
Width	10.4 cm 4.1 in

Regulatory Compliance/Certifications

Product Specifications

COMMScope®

SSH-12-4



Agency

ISO 9001:2008

Classification

Designed, manufactured and/or distributed under this quality management system