




760132670 | R-048-LZ-8W-F12BK/25D

Indoor/Outdoor Riser Rated Stranded Loose Tube Gel-Free Cable with Aluminum Interlocking Armor with a Riser Rated Outer Jacket

Representative Image



General Specifications

Cable Type	Stranded loose tube
Construction Type	Armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber
Total Fiber Quantity	48
Aarmor Type	Interlocking aluminum
Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Fiber Type, quantity	48
Fibers Per Subunit, quantity	12
Jacket Color	Black
Jacket UV Resistance	UV stabilized

Dimensions

Buffer Tube/Subunit Diameter	2.50 mm 0.10 in
Cable Weight	320.0 kg/km 215.0 lb/kft
Diameter Over Armor	18.40 mm 0.72 in
Diameter Over Jacket	20.50 mm 0.81 in
Filler, quantity	1
Subunit, quantity	4

Physical Specifications

760132670 | R-048-LZ-8W-F12BK/25D

Minimum Bend Radius, loaded	40.9 cm		16.1 in
Minimum Bend Radius, unloaded	28.6 cm		11.3 in
Tensile Load, long term, maximum	400 N		90 lbf
Tensile Load, short term, maximum	1335 N		300 lbf
Vertical Rise, maximum	125.0 m		410.1 ft

Flame Test Specifications

Flame Test Listing	NEC OFCR (ETL) and c(ETL)
Flame Test Method	UL 1666

Environmental Specifications

Environmental Space	Riser
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

Mechanical Test Specifications

Compression	483 lb/in		85 N/mm
Compression Test Method	FOTP-41		IEC 60794-1-2, Section 7
Flex	25 cycles		
Flex Test Method	FOTP-24		IEC 60794-1-2, Section 10
Impact	25.81 ft lb		35.00 N-m
Impact Test Method	FOTP-25		IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads		
Strain Test Method	FOTP-33		IEC 60794-1-2, Section 5
Twist	10 cycles		
Twist Test Method	FOTP-85		IEC 60794-1-2, Section 11
Water Penetration	24 h		
Water Penetration Test Method	FOTP-82		IEC 60794-1-2, Section 24

Environmental Test Specifications

Cable Freeze	-2 °C		28 °F
Cable Freeze Test Method	FOTP-98		
Heat Age	-40 °C to +85 °C		(-40 °F to +185 °F)
Heat Age Test Method	Not applicable		
Low High Bend	-30 °C to +60 °C		(-22 °F to +140 °F)
Low High Bend Test Method	FOTP-28		IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C		(-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3		IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-104-696-2001		EN 187105		Telcordia GR -409-CORE Issue 2
-------------------------------	--------------------------	--	-----------	--	--------------------------------

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

760132670 | R-048-LZ-8W-F12BK/25D

RoHS 2002/95/EC
ISO 9001:2008

Compliant
Designed, manufactured and/or distributed under this quality management system



Included Products

CS-8W-IOLT (Product Component—not orderable) — TeraSPEED® OS2 Singlemode Fiber