




760135103 | P-072-DS-CM-

FMUBR/8W036/5L036

Plenum Distribution Cable, 72 fiber multi-unit with 12 fiber subunits

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	Composite fiber LazrSPEED® 300, 50 µm multimode fiber TeraSPEED®, zero water peak singlemode fiber
Total Fiber Quantity	72
Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Fiber Type, quantity	36
Fibers Per Subunit, quantity	12
Jacket Color	Brown
Second Fiber Type	LazrSPEED® 300, 50 µm multimode fiber
Second Fiber Type, quantity	36

Dimensions

Buffer Tube/Subunit Diameter	5.90 mm 0.23 in
Cable Weight	237.0 lb/kft 353.0 kg/km
Diameter Over Jacket	19.10 mm 0.75 in
Subunit, quantity	6

Physical Specifications

Minimum Bend Radius, loaded	28.7 cm 11.3 in
-----------------------------	-------------------

760135103 | P-072-DS-CM-FMUBR/8W036/5L036

Minimum Bend Radius, unloaded	19.1 cm		7.5 in
Tensile Load, long term, maximum	1335 N		300 lbf
Tensile Load, short term, maximum	1000 lbf		4450 N
Vertical Rise, maximum	386.0 m		1266.4 ft

Flame Test Specifications

Flame Test Listing	NEC OFNP (ETL) and c(ETL)
Flame Test Method	NFPA 262

Environmental Specifications

Environmental Space	Plenum
Installation Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression	10 N/mm		57 lb/in
Compression Test Method	FOTP-41		IEC 60794-1-2, Section 7
Flex	100 cycles		
Flex Test Method	FOTP-104		IEC 60794-1-2, Section 10
Impact	4.34 ft lb		5.88 N-m
Impact Test Method	FOTP-25		IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads		
Strain Test Method	FOTP-33		IEC 60794-1-2, Section 5
Twist	10 cycles		
Twist Test Method	FOTP-85		IEC 60794-1-2, Section 11

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-28 IEC 60794-1-2, Section 28
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596-2001 Telcordia GR-409-CORE Issue 2
-------------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5L-TB (Product Component—not orderable) — LazrSPEED® 300 OM3 Multimode Fiber

CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber