


760135327 | M-006-DN-8W-  
F06NS/40G/GSM

Self-Support Figure-8 Single Jacket Non-Armor Arid-Core Drop Cable

Representative Image



General Specifications

Cable Type	Central loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber
Total Fiber Quantity	6
Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Fiber Type, quantity	6
Fibers Per Subunit, quantity	6
Jacket Color	Black
Jacket UV Resistance	UV stabilized

Dimensions

Buffer Tube/Subunit Diameter	4.00 mm   0.16 in
Cable Weight	46.0 lb/kft   69.0 kg/km
Diameter Over Jacket	6.80 mm   0.27 in
Diameter Over Messenger Jacket	3.40 mm   0.13 in
Height Over Jacket	11.50 mm   0.45 in
Subunit, quantity	1

Physical Specifications

760135327 | M006-DN-8WF06NS/40G/GSM

Minimum Bend Radius, loaded	10.2 cm		4.0 in
Minimum Bend Radius, unloaded	6.8 cm		2.7 in
Tensile Load, long term, maximum	400 N		90 lbf
Tensile Load, short term, maximum	1334 N		300 lbf
Vertical Rise, maximum	1938.0 ft		591.0 m

## Environmental Specifications

Environmental Space	Aerial, self-support		Buried
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)		
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)		
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)		

## Mechanical Test Specifications

Compression	10 N/mm		57 lb/in
Compression Test Method	FOTP-41		IEC 60794-1-2, Section 7
Flex	35 cycles		
Flex Test Method	FOTP-24		IEC 60794-1-2, Section 10
Impact	1.63 ft lb		2.21 N-m
Impact Test Method	FOTP-25		IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads		
Strain Test Method	FOTP-33		IEC 60794-1-2, Section 5
Twist	10 cycles		
Twist Test Method	FOTP-85		IEC 60794-1-2, Section 11
Water Penetration	24 h		
Water Penetration Test Method	FOTP-82		IEC 60794-1-2, Section 24

## Environmental Test Specifications

Cable Freeze	-2 °C		28 °F
Cable Freeze Test Method	FOTP-98		
Drip	70 °C		158 °F
Drip Test Method	FOTP-81		IEC 60794-1-2, Section 17
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)		
Heat Age Test Method	Not applicable		
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)		
Low High Bend Test Method	FOTP-28		IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)		
Temperature Cycle Test Method	FOTP-3		IEC 60794-1-2, Section 22

## Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-110-717-2003		EN 187105		Telcordia GR -20-CORE Issue 3
-------------------------------	--------------------------	--	-----------	--	-------------------------------

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

---

760135327 | M006-DN-8W-F06NS/40G/GSM

## Included Products

---

CS-8W-LT (Product Component—not orderable) — TeraSPEED® OS2 Singlemode Fiber