


760026393 | R-024-DS-CM-  
FSUOR/8W012/6F012  
**Riser Distribution Cable, 24 fiber single-unit**

## Representative Image



## General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

## Construction Materials

Fiber Type Solution	Composite fiber   OptiSPEED®, 62.5 µm multimode fiber   TeraSPEED®, zero water peak singlemode fiber
Total Fiber Quantity	24
Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Fiber Type, quantity	12
Jacket Color	Orange
Second Fiber Type	OptiSPEED®, 62.5 µm multimode fiber
Second Fiber Type, quantity	12

## Dimensions

Cable Weight	38.0 lb/kft   56.0 kg/km
Diameter Over Jacket	8.40 mm   0.33 in

## Physical Specifications

Minimum Bend Radius, loaded	12.5 cm   4.9 in
-----------------------------	------------------

760026393 | R-024-DS-CM-FSUOR/8W012/6F012

Minimum Bend Radius, unloaded	8.4 cm   3.3 in
Tensile Load, long term, maximum	400 N   90 lbf
Tensile Load, short term, maximum	1335 N   300 lbf
Vertical Rise, maximum	500.0 m   1640.4 ft

## Flame Test Specifications

Flame Test Listing	NEC OFNR (ETL) and c(ETL)
Flame Test Method	UL 1666

## Environmental Specifications

Environmental Space	Riser
Installation Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## Mechanical Test Specifications

Compression	10 N/mm   57 lb/in
Compression Test Method	FOTP-41   IEC 60794-1-2, Section 7
Flex	100 cycles
Flex Test Method	FOTP-104   IEC 60794-1-2, Section 10
Impact	4.34 ft lb   5.88 N-m
Impact Test Method	FOTP-25   IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1-2, Section 11

## Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-28   IEC 60794-1-2, Section 28
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1-2, Section 22

## Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596-2001   Telcordia GR-409-CORE Issue 2
-------------------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

---

CS-6F-TB (Product Component—not orderable) — OptiSPEED® OM1 Multimode Fiber

CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber