


760112896 | D-006-LN-5L-F06NS/LTS
Light Duty Single Jacket All-Dielectric Outdoor Stranded Loose Tube Arid-Core Construction Cable

Representative Image



General Specifications

Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	LazrSPEED® 300, 50 µm multimode fiber
Total Fiber Quantity	6
Fiber Type	LazrSPEED® 300, 50 µm multimode fiber
Fiber Type, quantity	6
Fibers Per Subunit, quantity	6
Jacket Color	Black
Jacket UV Resistance	UV stabilized

Dimensions

Buffer Tube/Subunit Diameter	2.50 mm 0.10 in
Cable Weight	35.0 lb/kft 52.0 kg/km
Diameter Over Jacket	9.30 mm 0.37 in
Filler, quantity	3
Subunit, quantity	1

Physical Specifications

760112896 | D-006-IN-5L-F06NS/LTS

Minimum Bend Radius, loaded	18.7 cm 7.4 in
Minimum Bend Radius, unloaded	9.3 cm 3.7 in
Tensile Load, long term, maximum	90 lbf 400 N
Tensile Load, short term, maximum	1335 N 300 lbf
Vertical Rise, maximum	788.0 m 2585.3 ft

Environmental Specifications

Environmental Space	Aerial, lashed Buried
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

Mechanical Test Specifications

Compression	125 lb/in 22 N/mm
Compression Test Method	FOTP-41 IEC 60794-1-2, Section 7
Flex	35 cycles
Flex Test Method	FOTP-24 IEC 60794-1-2, Section 10
Impact	2.17 ft lb 2.94 N-m
Impact Test Method	FOTP-25 IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1-2, Section 11
Water Penetration	24 h
Water Penetration Test Method	FOTP-82 IEC 60794-1-2, Section 24

Environmental Test Specifications

Cable Freeze	-2 °C 28 °F
Cable Freeze Test Method	FOTP-98
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-28 IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-87-640-2006 EN 187105
-------------------------------	-------------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5L-LT (Product Component—not orderable) — LazrSPEED® 300 OM3 Multimode Fiber