


760122747 | Z-008-DN-8W-F08BK/20G

Indoor/Outdoor Low Smoke Zero Halogen Single Jacket All-Dielectric Arid-Core Drop Cable

Representative Image



## General Specifications

Cable Type	Riser rated low smoke
Construction Type	Non-armored
Subunit Type	Gel-filled

## Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber
Total Fiber Quantity	8
Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Fiber Type, quantity	8
Fibers Per Subunit, quantity	8
Jacket Color	Black
Jacket UV Resistance	UV stabilized

## Dimensions

Buffer Tube/Subunit Diameter	2.00 mm   0.08 in
Cable Weight	30.0 lb/kft   44.0 kg/km
Diameter Over Jacket	6.10 mm   0.24 in
Subunit, quantity	1

## Physical Specifications

Minimum Bend Radius, loaded	9.1 cm		3.6 in
Minimum Bend Radius, unloaded	6.1 cm		2.4 in
Tensile Load, long term, maximum	400 N		90 lbf
Tensile Load, short term, maximum	1334 N		300 lbf
Vertical Rise, maximum	927.0 m		3041.3 ft

## Flame Test Specifications

Flame Test Listing	NEC OFNR-LS (ETL) and c(ETL)			
Flame Test Method	IEC 60332-3		IEC 60754-2	IEC 61034-2   IEEE 383   UL 1666   UL 1685

## Environmental Specifications

Environmental Space	Aerial, lashed		Buried		Low Smoke Zero Halogen (LSZH)		Riser
Installation Temperature	-20 °C to +70 °C (-4 °F to +158 °F)						
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)						
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)						

## Mechanical Test Specifications

Compression	10 N/mm		57 lb/in
Compression Test Method	FOTP-41		IEC 60794-1-2, Section 7
Flex	35 cycles		
Flex Test Method	FOTP-24		IEC 60794-1-2, Section 10
Impact	1.63 ft lb		2.21 N-m
Impact Test Method	FOTP-25		IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads		
Strain Test Method	FOTP-33		IEC 60794-1-2, Section 5
Twist	10 cycles		
Twist Test Method	FOTP-85		IEC 60794-1-2, Section 11
Water Penetration	24 h		
Water Penetration Test Method	FOTP-82		IEC 60794-1-2, Section 24

## Environmental Test Specifications

Cable Freeze	-2 °C		28 °F
Cable Freeze Test Method	FOTP-98		
Drip	70 °C		158 °F
Drip Test Method	FOTP-81		IEC 60794-1-2, Section 17
Heat Age Test Method	Not applicable		
Low High Bend	-20 °C to +60 °C (-4 °F to +140 °F)		
Low High Bend Test Method	FOTP-28		IEC 60794-1-2, Section 28
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)		
Temperature Cycle Test Method	FOTP-3		IEC 60794-1-2, Section 22

## Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-110-717-2003		EN 187105		Telcordia GR -409-CORE Issue 2
-------------------------------	--------------------------	--	-----------	--	--------------------------------

760122747 | Z-008-DN-8W-F08BK/20G

## Regulatory Compliance/Certifications

### Agency

RoHS 2002/95/EC  
ISO 9001:2008

### Classification

Compliant  
Designed, manufactured and/or distributed under this quality management system



## Included Products

CS-8W-IOLT (Product Component—not orderable) — TeraSPEED® OS2 Singlemode Fiber