



760135616 | O-024-L3-8W-F12NS

Triple Jacket Double Armor Outdoor Cable Arid-Core Construction Stranded Loose Tube

Representative Image

General Specifications

Cable Type	Stranded loose tube
Construction Type	Armored
Subunit Type	Gel-filled

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber
Total Fiber Quantity	24
Armor Type	Corrugated steel
Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Fiber Type, quantity	24
Fibers Per Subunit, quantity	12
Jacket Color	Black
Jacket UV Resistance	UV stabilized

Dimensions

Buffer Tube/Subunit Diameter	3.00 mm 0.12 in
Cable Weight	259.0 lb/kft 386.0 kg/km
Diameter Over Jacket	20.50 mm 0.81 in
Filler, quantity	3
Subunit, quantity	2

Physical Specifications

Minimum Bend Radius, loaded	30.8 cm 12.1 in
Minimum Bend Radius, unloaded	20.5 cm 8.1 in
Tensile Load, long term, maximum	180 lbf 800 N
Tensile Load, short term, maximum	2700 N 607 lbf
Vertical Rise, maximum	212.0 m 695.5 ft

Environmental Specifications

Environmental Space	Aerial, lashed Buried
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

Mechanical Test Specifications

Compression	250 lb/in 44 N/mm
-------------	---------------------

760135616 | O-024L3-8WF12NS

Compression Test Method	FOTP-41 IEC 60794 -1-2, Section 7
Flex	35 cycles
Flex Test Method	FOTP-24 IEC 60794 -1-2, Section 10
Impact	4.88 ft lb 6.62 N-m
Impact Test Method	FOTP-25 IEC 60794 -1-2, Section 8
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794 -1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794 -1-2, Section 11
Water Penetration	24 h
Water Penetration Test Method	FOTP-82 IEC 60794 -1-2, Section 24

Environmental Test Specifications

Cable Freeze	-2 °C 28 °F
Cable Freeze Test Method	FOTP-98
Drip	70 °C 158 °F
Drip Test Method	FOTP-81 IEC 60794 -1-2, Section 17
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-28 IEC 60794 -1-2, Section 28
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794 -1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-87-640-2006 EN 187105 Telcordia GR -20-CORE Issue 3
-------------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-8W-LT (Product Component—not orderable) — TeraSPEED® OS2 Singlemode Fiber