




760140624 | P-006-LZ-6F-F06BK/25D  
**FiberGuard Indoor/Outdoor Plenum Rated Stranded Loose Tube Arid-Core® Cable**

## Representative Image



## General Specifications

Cable Type	Stranded loose tube
Construction Type	Armored
Subunit Type	Gel-free

## Construction Materials

Fiber Type Solution	OptiSPEED®, 62.5 µm multimode fiber
Total Fiber Quantity	6
Armor Type	Interlocking aluminum
Fiber Type	OptiSPEED®, 62.5 µm multimode fiber
Fiber Type, quantity	6
Fibers Per Subunit, quantity	6
Jacket Color	Black
Jacket UV Resistance	UV stabilized

## Dimensions

Buffer Tube/Subunit Diameter	2.50 mm   0.10 in
Cable Weight	192.0 lb/kft   286.0 kg/km
Diameter Over Armor	15.90 mm   0.63 in
Diameter Over Jacket	17.90 mm   0.70 in
Filler, quantity	4
Subunit, quantity	1

## Physical Specifications

760140624 | P-006-LZ-6F-F06BK/25D

---

Minimum Bend Radius, loaded	35.8 cm		14.1 in
Minimum Bend Radius, unloaded	25.1 cm		9.9 in
Tensile Load, long term, maximum	90 lbf		400 N
Tensile Load, short term, maximum	1335 N		300 lbf
Vertical Rise, maximum	143.0 m		469.2 ft

## Flame Test Specifications

---

Flame Test Listing	NEC OFCP (ETL) and c(ETL)
Flame Test Method	NFPA 262

## Environmental Specifications

---

Environmental Space	Plenum
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

## Mechanical Test Specifications

---

Compression	483 lb/in		85 N/mm
Compression Test Method	FOTP-41		IEC 60794-1-2, Section 7
Flex	25 cycles		
Flex Test Method	FOTP-104		IEC 60794-1-2, Section 10
Impact	25.81 ft lb		35.00 N-m
Impact Test Method	FOTP-25		IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads		
Strain Test Method	FOTP-33		IEC 60794-1-2, Section 5
Twist	10 cycles		
Twist Test Method	FOTP-85		IEC 60794-1-2, Section 11
Water Penetration	24 h		
Water Penetration Test Method	FOTP-82		IEC 60794-1-2, Section 24

## Environmental Test Specifications

---

Cable Freeze	-2 °C		28 °F
Cable Freeze Test Method	FOTP-98		
Heat Age	-40 °C to +85 °C	(-40 °F to +185 °F)	
Heat Age Test Method	Not applicable		
Low High Bend	-30 °C to +60 °C	(-22 °F to +140 °F)	
Low High Bend Test Method	FOTP-28		IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C	(-40 °F to +158 °F)	
Temperature Cycle Test Method	FOTP-3		IEC 60794-1-2, Section 22

## Qualification Specifications

---

Cable Qualification Standards	ANSI/ICEA S-104-696-2001		EN 187105		Telcordia GR -409-CORE Issue 2
-------------------------------	--------------------------	--	-----------	--	--------------------------------

## Regulatory Compliance/Certifications

760140624 | P-006-LZ-6F-F06BK/25D

**Agency**

RoHS 2002/95/EC  
ISO 9001:2008

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system



## Included Products

---

CS-6F-LT (Product Component—not orderable) — OptiSPEED® OM1 Multimode Fiber