

**Overview**

- The AL600ULXD power supply converts a 115VAC or 230VAC / 50/60Hz input, to a 12VDC or 24VDC non-power limited output.

Specifications

- Switch selectable 12VDC or 24VDC non-power limited output.
- 12VDC or 24VDC @ 6 amp supply current.
- Input 115VAC / 60Hz, 1.9 amp or 230VAC 50/60Hz, .95 amp.
- Maximum charge current .7 amp.
- Filtered and electronically regulated output.
- Built-in charger for sealed lead acid or gel type batteries.
- Automatic switch over to stand-by battery when AC fails.
- AC input and DC output LED indicators.
- AC fail supervision (form "C" contacts).
- Low battery and battery presence supervision (form "C" contacts).
- Short circuit and thermal overload protection.
- Unit is complete with power supply, enclosure, cam lock and open frame transformers.
- Includes battery leads.

Agency Approvals

- UL 294 UL Listed for Access Control System Units.
- UL 1481 UL Listed Standard for Safety for Fire Protective Signaling Systems.



European Conformity.

Enclosure Dimensions

15.5"H x 12"W x 4.5"D

