



## 760072082 | 1100A-GS3-1U

**GigaSPEED® XL 1100AGS3 U/UTP 1U Panel Kit - Angled Multimedia Distribution Hardware**

### Replaced By:

760152785  
360-A-E-KIT-1U

SYSTIMAX 360™ GigaSPEED® X10D and GigaSPEED® XL Evolve Angled 1U U/UTP Panel Kit

### Dimensions

Depth	40.64 mm   1.60 in
Diameter Over Dielectric, maximum	1.168 mm   0.046 in
Diameter Over Dielectric, minimum	0.762 mm   0.030 in
Height	44.45 mm   1.75 in
Width	482.60 mm   19.00 in

### Electrical Specifications

ANSI/TIA Category	6
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

### Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

Brand	GigaSPEED® XL   SYSTIMAX®
Modules, quantity	4
Product Type	Panel
Total Ports, quantity	24
Color	Black
Package, quantity	1
Rack Type	EIA 19 in
Rack Units	1

### Mechanical Specifications

Panel Style	Angled
Conductor Gauge, solid	22 AWG   24 AWG   26 AWG

760072082 | 1100AGS3-1U

Conductor Gauge, stranded	22 AWG   24 AWG
Conductor Type	Solid   Stranded (7 strands)
Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf   133 N
Rear Termination Contact Plating	Precious metals
Rear Termination Type	IDC
Wiring	T568A   T568B

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

