



## 760094375 | VP360-HCM-Cover-19

VisiPatch® 360 Horizontal Trough Cover 19"

### Dimensions

Width 482.60 mm | 19.00 in

### Environmental Specifications

Flammability Rating UL 94 V-0  
Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)  
Safety Standard cETL | ETL

### General Specifications

Product Type Cable manager  
Brand SYSTIMAX® | VisiPatch® 360  
Package, quantity 1

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

