




760128231 | O-024-LN-8W-F12NS/20T

Mini Single Jacket All-Dielectric Outdoor Stranded Loose Tube Arid-Core® Construction Cable

Representative Image



General Specifications

Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber
Total Fiber Quantity	24
Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Fiber Type, quantity	24
Fibers Per Subunit, quantity	12
Jacket Color	Black
Jacket UV Resistance	UV stabilized

Dimensions

Buffer Tube/Subunit Diameter	2.00 mm   0.08 in
Cable Weight	48.0 lb/kft   72.0 kg/km
Diameter Over Jacket	9.50 mm   0.37 in
Filler, quantity	4
Subunit, quantity	2

Physical Specifications

Minimum Bend Radius, loaded	14.3 cm   5.6 in
Minimum Bend Radius, unloaded	9.5 cm   3.7 in
Tensile Load, long term, maximum	180 lbf   800 N

760128231 | O-024LN-8WF12NS/20T

Tensile Load, short term, maximum 2700 N | 607 lbf  
Vertical Rise, maximum 1142.0 m | 3746.7 ft

## Environmental Specifications

Environmental Space	Aerial, lashed   Buried
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

## Mechanical Test Specifications

Compression	125 lb/in   22 N/mm
Compression Test Method	FOTP-41   IEC 60794-1-2, Section 7
Flex	35 cycles
Flex Test Method	FOTP-24   IEC 60794-1-2, Section 10
Impact	2.17 ft lb   2.94 N-m
Impact Test Method	FOTP-25   IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1-2, Section 11
Water Penetration	24 h
Water Penetration Test Method	FOTP-82   IEC 60794-1-2, Section 24

## Environmental Test Specifications

Cable Freeze	-2 °C   28 °F
Cable Freeze Test Method	FOTP-98
Drip	70 °C   158 °F
Drip Test Method	FOTP-81   IEC 60794-1-2, Section 17
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-28   IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1-2, Section 22

## Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-87-640-2006   EN 187105   Telcordia GR -20-CORE Issue 3
-------------------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

---

CS-8W-LT (Product Component—not orderable) — TeraSPEED® OS2 Singlemode Fiber