



PD8UL

### **Overview**

- PD8UL Sub-Assembly power distribution module converts a single DC or AC input into eight (8) individually fuse protected outputs.

### **Specifications**

#### **Input:**

- 12VDC or 24VDC up to 10 amp,  
24VAC or 28VAC up to 12 amp\*  
(total output current should not exceed max current rating of power supply employed).

#### **Output:**

- Eight (8) individual fuse protected outputs.
- Fuses rated @ 3.5 amp/250V.
- Surge suppression.

#### **Electrical:**

- Operating temperature: 0° C to 49° C ambient.

#### **Mechanical:**

- Product weight (approx.): 1.38 lbs
- Shipping weight (approx.): 1.4 lbs.

#### **Features:**

- Power LED indicator.

\* AC not evaluated by UL.

### **Agency Approvals**

**SECURITY  
SIGNALLING**

**LISTED**

UL Listed Sub-Assembly for Access Control System Units (UL 294) and for Power Supplies for Fire Protective Signaling Systems (UL 1481).

### **Board Dimensions (approximate)**

5.25"H x 3.25"W x 1"D

### **Mounting Diagram**

