



SMP7PMCTX

Overview

This unit will convert a 115VAC / 60Hz input, into a regulated 12VDC or 24VDC output.

Specifications

- | | |
|--|---|
| <ul style="list-style-type: none">• 12VDC or 24VDC selectable output.• 6 amp of continuous supply current output.• Input 115VAC rating @ 1.45 amp.• Filtered and electronically regulated outputs.• Short circuit and thermal overload protection.• Built-in charger for sealed lead acid or gel type batteries.• Maximum charge rating @ 0.7 amp.• Automatic switch over to stand-by battery when AC fails (zero voltage drop).• AC fail supervision (form “C” contacts). | <ul style="list-style-type: none">• Low battery supervision (form “C” contacts).• AC input and DC output LED indicators.• Power on-off switch.• Power supply, enclosure, cam lock and battery leads.• Enclosure:<ul style="list-style-type: none">- Combination knockouts are 1/2” and 3/4”- Accommodates up to two (2) 12VDC/7AH batteries. <p>SMP7PMCTX weights (approximate):
Product weight: 7.9 lbs.
Shipping weight: 9.0 lbs.</p> |
|--|---|

Enclosure Dimensions

13.5"H x 13"W x 3.25"D

