
Overview

- Converts a 24VDC input into a regulated 12VDC output.



Specifications

- Converts a 24VDC input to a 12VDC output.
 - 12VDC @ 2 amp max.
 - Power LED.
 - Electronically filtered and regulated output.
 - Built-in overload protection.
 - Screw terminal block (wire gauge 14-20AWG).
 - High impact insulated housing.
 - Compact design allows for integration in a wide range of camera housings.
- Dimensions (approximate): 1.625"L x 2.375"W x 1"H
VR3T weights (approximate):
Product weight: 0.13 lbs.
Shipping weight: 0.15 lbs.

Applications

- Power for 12VDC CCTV cameras and accessories, Fiber Optic Transmitters, REX PIR's, Prox Readers, etc.

Agency Approvals