

INSULATE
SEAL
PROTECT

4:1
SHRINK RATIO



THIN WALL ADHESIVE LINED CROSS-LINKED POLYOLEFIN

SEMI-RIGID, DUAL WALL HEAT SHRINK TUBING DESIGNED TO SEAL & ENVIRONMENTALLY PROTECT THE TOUGHEST SPLICES IN THE MOST DEMANDING & RUGGED APPLICATIONS.

FEATURES AND BENEFITS

- 4:1 shrink ratio allows for fewer sizes to cover numerous splice configurations and diameters
- Environmentally seal and protect, splices and terminals in automotive, on highway/off road heavy equipment applications
- Highly resistant to Diesel and other common automotive fluids and solvents
- Semi-rigid and mechanically tough outer jacket provides added strain relief and excellent abrasion protection
- Thick adhesive liner forms an effective barrier against fluids and moisture penetration
- Continuous operating temperature: -40°C to 130°C
- Shrink temperature: 125°C

STANDARDS


- Meets most automotive, on highway/off road heavy equipment & electronic standards & requirements

TYPICAL APPLICATIONS

- Environmental sealing of in-line splices, connectors & terminals
- Strain relief
- Abrasion protection and electrical insulation of automotive wiring harness splices and valuable components
- On-highway and off-road heavy equipment applications
- Fleet & marine sealing & protection



SIZE	EXPANDED		TOTAL RECOVERED				ADHESIVE WALL	
	INTERNAL DIAMETER		MAX ID		TOTAL WALL			
	MM	(INCH)	MM	(INCH)	MM	(INCH)	MM	(INCH)
1	6.60	0.260	1.27	0.050	1.40	0.055	0.76	0.030
2	8.64	0.340	1.52	0.060	1.68	0.066	0.91	0.036
3	11.68	0.460	2.03	0.080	2.11	0.083	1.22	0.048
4	19.30	0.760	3.81	0.150	2.64	0.104	1.60	0.063



INSTALLATION

- DSG-Canusa offers a comprehensive selection of technically advanced shrink appliances that ensure process stability and repeatability
- Minimum recovery temperature: 125°C
- Adhesive activation temperature: 110°C

ORDERING

- Select a dimension which will shrink snugly over the component to be covered. If recovery is restricted the resultant wall thickness will be less than specified.
 - Select Options:
 - Colour: Black (BK)
 - Length: Standard cut length, 4 ft stick or spool
 - Please specify the product name plus the options you require
- Order Example: CDR, 3, black, 65 mm length

Please contact your Customer Service Representative for information on custom sizes, lengths and material data sheet.

All information contained in this data sheet is believed to be reliable. We advise, however, that customers should separately evaluate the suitability of our products for their particular application. DSG-Canusa and ShawCor give no guarantees in respect of the accuracy or sufficiency of the information presented and disclaim any liability regarding its use. Our responsibilities are only those listed in our Standard Terms and Conditions of Sale for these products. In no instance will we be liable for any eventual, indirect or consequential damage or damages arising from the sale, resale, transfer, use or misuse of the product.