




4604805/10 | 2003 TEAL REEL

Sunlight and Oil Resistant Category 5e U/UTP 2003 Cable, non-plenum, teal jacket, 4 pair count, 1000 ft (305 m) length, reel

## Cross Section Drawing



## Construction Materials

Conductor Material	Bare copper
Drain Wire Material	Tinned copper
Insulation Material	Polyolefin
Jacket Material	PVC
Shield (Tape) Material	Polyester/Aluminum tape

## Dimensions

Cable Length	305 m   1000 ft
Cable Weight	29.06 lb/kft
Diameter Over Bundle	4.191 mm   0.165 in
Diameter Over Jacket	6.350 mm   0.250 in
Jacket Thickness	0.762 mm   0.030 in

## Electrical Specifications

ANSI/TIA Category	5e
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m
Delay Skew	45 ns

4604805/10 | 2003 TEAL REEL

Mutual Capacitance	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	69 %
Operating Frequency, maximum	100 MHz
Transmission Standards	ANSI/TIA-568-C.2
Safety Voltage Rating	300 V
Dielectric Strength, minimum	1500 Vac   2500 Vdc

## Environmental Specifications

Environmental Space	Non-plenum
Flame Test Method	CMR
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

## General Specifications

Brand	Uniprise®
Cable Component Type	Horizontal
Cable Type	F/UTP (shielded)
Pairs, quantity	4
Jacket Color	Teal
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Packaging Type	Reel
Product Number	2003

## Mechanical Specifications

Pulling Tension, maximum	11 kg   25 lb
--------------------------	---------------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Electrical Performance

Std	Standard (ANSI/TIA-568)		
IL	Insertion Loss (dB/100m)	PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)
NEXT	Near End Crosstalk (dB/100m)	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)
PSNEXT	Power Sum Near End Crosstalk (db/100m)	RL	Return Loss (dB)

Freq. MHz	IL	NEXT	ACR	PSNEXT	PSACR	ACRF	PSACRF	RL
	Std	Std	Std	Std	Std	Std	Std	Std
1	2.0	65.3	63.3	62.3	60.3	63.8	60.8	20.0
4	4.1	56.3	52.2	53.3	49.2	51.8	48.8	23.0
8	5.8	51.8	46.0	48.8	43.0	45.7	42.7	24.5
10	6.5	50.3	43.8	47.3	40.8	43.8	40.8	25.0
16	8.2	47.2	39.0	44.2	36.0	39.7	36.7	25.0
20	9.3	45.8	36.5	42.8	33.5	37.8	34.8	25.0
25	10.4	44.3	33.9	41.3	30.9	35.8	32.8	24.3
31.25	11.7	42.9	31.2	39.9	28.2	33.9	30.9	23.6
62.5	17.0	38.4	21.4	35.4	18.4	27.9	24.9	21.5
100	22.0	35.3	13.3	32.3	10.3	23.8	20.8	20.1