


Product Data Sheet

Security/Alarm/Access Control/Sound Low-voltage Cable Nonshielded Nonplenum



Product Description

PVC

Bare copper conductor

UL Listed Type CMR, CL3R

Applications

For use in security systems, intercom systems, sound/audio systems, access control, power-limited controls.

Specifications

- CONDUCTOR: Bare copper, stranded or solid
- INSULATION: Polyvinyl chloride (PVC)
- OVERALL JACKET: Gray polyvinyl chloride (PVC)
- STANDARDS: NEC: CMR (22-16 AWG), CL3R (14-12 AWG); NEC Article(s) 800, 725
- RATINGS: 75 °C, 300 V

Product Data Sheet

Standard color is gray, other colors available. Most items available on spools or boxes except on larger O.D. products. Diameters and weights may vary among manufacturers. Paired conductors also available.

Part No.	Conductor Size AWG	No. of Conductors	Rating	Insulation	Insulation Thickness (in.)	Overall Jacket Thickness (in.)	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.
AL-2202C-1-1N-09	22 (SOL)	2	CMR	PVC	0.007	0.015	0.122	8
AL-2202C-2-1N-09	22	2	CMR	PVC	0.007	0.015	0.120	11
AL-2203C-2-1N-09	22	3	CMR	PVC	0.007	0.015	0.131	14
AL-2204C-2-1N-09	22	4	CMR	PVC	0.007	0.015	0.142	16
AL-2204C-1-1N-09	22 (SOL)	4	CMR	PVC	0.007	0.015	0.135	14
AL-2206C-2-1N-09	22	6	CMR	PVC	0.007	0.015	0.170	24
AL-2208C-2-1N-09	22	8	CMR	PVC	0.007	0.018	0.190	31
AL-2210C-2-1N-09	22	10	CMR	PVC	0.007	0.020	0.210	39
AL-2212C-2-1N-09	22	12	CMR	PVC	0.007	0.022	0.229	15
AL-2002C-2-1N-09	20	2	CMR	PVC	0.008	0.015	0.148	21
AL-2003C-2-1N-09	20	3	CMR	PVC	0.010	0.015	0.161	26
AL-2004C-2-1N-09	20	4	CMR	PVC	0.010	0.018	0.178	26
AL-1802C-2-1N-09	18	2	CMR	PVC	0.009	0.015	0.172	16
AL-1803C-2-1N-09	18	3	CMR	PVC	0.009	0.015	0.187	30
AL-1804C-2-1N-09	18	4	CMR	PVC	0.009	0.018	0.203	37
AL-1806C-2-1N-09	18	6	CMR	PVC	0.009	0.020	0.226	52
AL-1808C-2-1N-09	18	8	CMR	PVC	0.009	0.020	0.242	66
AL-1602C-2-1N-09	16	2	CMR	PVC	0.009	0.018	0.198	30
AL-1604C-2-1N-09	16	4	CMR	PVC	0.009	0.020	0.234	54
AL-1402C-2-1N-09	14	2	CL3R	PVC	0.010	0.025	0.238	45
AL-1404C-2-1N-09	14	4	CL3R	PVC	0.010	0.025	0.286	74
AL-1202C-2-1N-09	12	2	CL3R	PVC	0.011	0.028	0.296	68