

ANIXTER

Technical Data Sheet

Anixter Part No:

BS5467-3C-0250-HAR

Description

stranded plain annealed copper conductors, XLPE insulation, cores laid up, PVC sheath, galvanised steel wire armour, PVC sheath (black). BS5467

Dimensions

Number of cores	3	no.
Nominal conductor size	25	mm ²
Conductor shape	Compacted Round	
Insulation thickness	0.9	mm
Inner sheath thickness	1.0	mm
Nominal inner sheath diameter	20.1	mm
Armour wire size	1.6	mm
Outer sheath thickness	1.7	mm
Nominal outer diameter	26.7	mm

Electrical Characteristics

Nominal voltage rating (U ₀ /U)	600/1000	Vrms
Maximum DC conductor resistance @ 20°C	0.727	ohm/km
Maximum AC conductor resistance @ 90°C	0.927	ohm/km
Reactance @ 50 Hz	0.0818	ohm/km
Impedance @ 90°C, 50Hz	0.931	ohm/km
Voltage drop	1.90	mV/A/m
Maximum DC armour resistance @ 20°C	2.50	ohm/km
Conductor short-circuit rating (1s)	3.57	kA
Armour short-circuit rating (1s)	2.85	kA
Sustained Current Ratings:		
Buried direct (15°C ground temperature, 1.2°C m/W)	183	A
In single-way duct (15°C ground temperature, 1.2°C m/W)	148	A
In air (25°C ambient temperature)	164	A

Physical Characteristics

Maximum conductor operating temperature	90	°C
Maximum conductor short-circuit temperature	250	°C
Maximum armour short-circuit temperature	200	°C
Conductor material	Stranded Class 2 plain annealed copper conductors to BS EN 60228	
Insulation material	XLPE Type GP8 to BS7655 Section 1.3	
Inner sheath material	PVC Type 9 to BS7655 Section 4.2	
Armour material	Mild galvanised steel wires to BS EN 10257-1	
Outer sheath material	PVC Type 9 to BS7655 Section 4.2	
Maximum pulling tension by conductor eye	470	kgf
Minimum bending radius	170	mm
Flame resistance	Flame retardant to BS EN 60332-1-2	
Weight	1550	kg/km

Core Identification: brown, blue, green/yellow

Issue No: 1

Drawn By: M S Fordham

Date: 14/09/2012