# **Search Technical Data Sheets**



**Technical Data Sheet** 

# **BRADY B-361B CLEAR POLYESTER FILM TAPE**

TDS No. B-361B Effective Date: 16-Jul-2008

## **Description:**

GENERAL Print Technology: Laser Material Type: Clear polyester Finish: Clear film with matte white printable zone coated ink Adhesive: Permanent acrylic

#### APPLICATIONS

WIre and cable identification

# REGULATORY

Brady B-361 is RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC.

### SPECIAL FEATURES

Brady B-361B is used in a self-laminating format which has a white printable or write-on zone and a translucent overlaminating area. Brady B-361B has good print smudge resistance, solvent resistance, and elevated temperature performance.

#### Details:

PHYSICAL PROPERTIES	TEST METHODS	AVERAGE RESULTS
Thickness	ASTM D 1000	
	-Substrate	0.0010 inch (0.025 mm)
	-Adhesive	0.0010 inch (0.025 mm)
	-Total	0.0020 inch (0.050 mm)
Adhesion to:	ASTM D 1000	
-Stainless Steel	20 minute dwell	34 oz/in (37 N/100 mm)
	24 hour dwell	38 oz/in (42 N/100 mm)
-Textured ABS	20 minute dwell	9 oz/in (10 N/100 mm)
	24 hour dwell	9 oz/in (10 N/100 mm)
-Polypropylene	20 minute dwell	16 oz/in (18 N/100 mm)
	24 hour dwell	16 oz/in (18 N/100 mm)
Tack	ASTM D 2979	
	Polyken™ Probe Tack	16 oz (450 g)
	1 second dwell	
Tensile Strength and Elongation	ASTM D 1000	
	-Machine Direction	17 lbs/in (298 N/100 mm), 50%
Application Temperature	Lowest application temperature to stainless steel	50°F (4°C)

The following testing is performed with the B-361B self-laminates printed with laser printer . Samples wrapped around 0.080" OD TFE jacketed wires and 0.250" OD MTW wires. Unprinted samples also applied to flat aluminum panels. All samples allowed to dwell 24 hours prior to testing.

PERFORMANCE PROPERTIES	TEST METHODS	TYPICAL RESULTS

High Service Temperature	30 days at 230°F (	. ,	Slight discoloration at 110°C; no visible effect to laser print. Material discolored but functional up to 130° C.
Low Service Temperature	30 days at -94°F (	-70°C)	No visible effect
Humidity Resistance	30 days at 100°F (	(37°C), 95% R. H.	No visible effect
UV Light Resistance	30 days in UV Sunlighter™ 100		No visible effect
Weatherability	ASTM G155, Cycl 30 days in Xenon Weatherometer		No visible effect
Salt Fog Resistance	ASTM B 117 30 days in 5% salt fog solution chamber		No visible effect
PERFORMANCE PROPERTY		SOLVENT RESISTANCE	

B-361B self-laminate samples were printed with laser printer. Samples wrapped around 0.080" OD TFE jacketed wires and 0.250" OD MTW wires and dwelled 24 hours prior to test. Unprinted samples also applied to flat aluminum panels. Testing consisted of 5 cycles of 10 minute immersions in the specified chemicals followed by 30 minute recovery periods. Testing was conducted at room temperature.

CHEMICAL REAGENT	SUBJECTIVE OBSERVATION OF VISUAL CHANGE				
	APPEARANCE OF MARKER ON 0.080" OD WIRE	APPEARANCE OF MARKER ON 0.250" OD WIRE	APPEARANCE OF FLAT LABEL ON ALUMINUM PANEL		
Methyl Ethyl Ketone	Severe unwrap	Slight unwrap	Slight adhesive ooze		
1,1,1-Trichloroethane	Slight unwrap	No visible effect	Slight adhesive ooze		
Isopropyl Alcohol	Slight unwrap	No visible effect	No visible effect		
Mineral Spirits	No visible effect	No visible effect	No visible effect		
JP-4 Jet Fuel	Slight unwrap	No visible effect	No visible effect		
JP-8 Jet Fuel	Slight unwrap font	No visible effect	No visible effect		
SAE 20 WT Oil	No visible effect	No visible effect	No visible effect		
Mil 5606 Oil	No visible effect	No visible effect	No visible effect		
Speedi Kut Cutting Oil 332	No visible effect	No visible effect	No visible effect		
Gasoline	Slight unwrap	Slight unwrap	Slight adhesive ooze		
Rust Veto® 377	No visible effect	No visible effect	No visible effect		
Skydrol® 500B-4	Slight unwrap	No visible effect	Slight adhesive ooze		
Super Agitene®	No visible effect	No visible effect	No visible effect		
Deionized Water	No visible effect	No visible effect	No visible effect		
3% Alconox® Detergent	No visible effect	No visible effect	No visible effect		

Laser printing legible in all test fluids.

Product testing, customer feedback, and history of similar products, support a customerperformance expectation of at least*two years from the date of receipt* for this product as long as this product is stored in its original packaging in an environment *below 80 degrees F (27 degrees C) and 60% RH*. We are confident that our product will perform well beyond this time frame. However, it remains the responsibility of the user to assess the risk of using such product. We encourage customers to develop functional testing protocols that will qualify a product's fitness for use, in their actual applications.

#### Trademarks:

Alconox® is a registered trademark of Alconox Co. Polyken<sup>™</sup> is a trademark of Testing Machines Inc. Rust Veto® is a registered trademark of the E.F. Houghton & Co. Skydrol® is a registered trademark of the Monsanto Company Sunlighter<sup>™</sup> is a trademark of the Test Lab Apparatus Company Super Agitene® is a registered trademark of Graymills Corporation ASTM: American Society for Testing and Materials (U.S.A.) SAE: Society of Automotive Engineers (U.S.A.) All S.I. Units (metric) are mathematically derived from U.S. conventional units.

**Note:** All values shown are averages and should not be used for specification purposes. Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

### WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2011 Brady Worldwide, Inc. | All Rights Reserved Material may not be reproduced or distributed in any form without written permission.

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289