

Overview

The AL1002ULADA are extremely cost effective voltage regulated remote NAC Power Extenders. They may be connected to any 24 volt Fire Alarm Control Panel (FACP). Primary applications include Notification Appliance Circuit (NAC) expansion (supports ADA requirements) and will provide auxiliary power to support system accessories.



AL1002ULADA

Specifications

- 24VDC rated @ 10 amp max.
- Two (2) Class A or four (4) Class B outputs.
- Two (2) Class A or two (2) Class B FACP inputs.
- Two (2) NC dry contact trigger inputs.
- Two (2) Class A or four (4) Class B indicating circuits.
- Two (2) Class B outputs may be paralleled for more power on an indicating circuit.
- One (1) Aux. Power Output @ 1 amp supply current (w/battery back up).
- Signal Circuit Trouble Memory - facilitates quickly locating intermittent system trouble and eliminates costly and unnecessary service calls. LED's indicate a prior fault (short, open, ground) has occurred on one or more signaling circuit outputs.
- 2-wire Horn/Strobe Sync mode allows audible notification appliances (Horns) to be silenced while visual notification appliances (Strobes) continue to operate.
- Horn/Strobe sync protocols include: CooperWheelock®, Gentex®, System Sensor®, Faraday, Amseco.
- Temporal Code 3 Mode.
- Steady Mode.
- Input to Output Follower Mode (maintains synchronization of notification appliance circuits).
- March Time.
- Compatible with 12VDC or 24VDC fire panels.
- Common trouble inputs and outputs.
- Ground fault detection.
- Input 115VAC.
- AC fail supervision (form "C" contacts).
- Low battery supervision (form "C" contacts).
- Battery presence supervision (form "C" contacts).
- Power supply, logic board, red enclosure, cam lock, transformer & battery leads.
- Enclosure:
 - Combination knockouts are 1/2" and 3/4"
 - Accommodates up to two (2) 12VDC/12AH batteries.

AL1002ULADA weights (approximate):

Product weight: 12 lbs.

Shipping weight: 13.3 lbs.

Agency Approvals



UL Listed Control Units and Accessories
for Fire Alarm Systems (UL 864) Ninth
Edition



MEAN Approved NYC Department of Buildings Approved.



California State Fire Marshal Approved.



Factory Mutual Approved.

Enclosure Dimensions

15.5"H x 12.23"W x 4.5"D

