



Overview

This UL Recognized power supply/charger converts a 115VAC/60Hz input into a single 12VDC non-power limited output.

Specifications

- 12VDC output.
- 10 amp of continuous supply current.
- Input 115VAC / 60Hz, 2.6 amp.
- Input fuse rated @ 5 amp/250V.
- Output fuse rated @ 15 amp/32V.
- Filtered and electronically regulated output.
- Short circuit and thermal overload protection.
- Built-in charger for sealed lead acid or gel type batteries.
- Maximum charge current 0.7 amp.
- Automatic switch over to stand-by battery when AC fails (zero voltage drop).
- AC fail supervision (form "C" contacts).
- Low battery supervision (form "C" contacts).
- Battery presence supervision (form "C" contacts).
- AC input and DC output LED indicators.

Agency Approvals



UL Recognized component for Access Control System Units (UL 294)

Board Dimensions (approximate):

4.5"W x 7.1"L x 1.75"H

