



Overview

- These multi-agency approved multi-output power supply/chargers convert a 115VAC/60Hz input into eight (8) Class 2 Rated 12VDC or 24VDC power limited outputs.

AL400ULPD8

- Fuses are rated @ 3.5 amp/250V.
- Grey enclosure.

AL400ULPD8R

- Red enclosure.

AL400ULPD8CB

- PTC's are rated @ 2.5 amp.
- Grey enclosure.

AL400ULPD8CBR

- Red enclosure.

Specifications

- | | |
|--|---|
| <ul style="list-style-type: none"> • 12VDC or 24VDC selectable outputs. • 12VDC @ 4 amp or 24VDC @ 3 amp supply current. • Class 2 Rated power limited outputs. • Eight (8) protected outputs. • Input 115VAC / 60Hz, 1.45 amp. • Input fuse rated @ 3.5 amp/250V. • Filtered and electronically regulated outputs. • Short circuit and thermal overload protection. • Built-in charger for sealed lead acid or gel type batteries. • Maximum charge current .7 amp. • Automatic switch over to stand-by battery when AC fails (zero voltage drop). | <ul style="list-style-type: none"> • AC fail supervision (form "C" contacts). • Low battery supervision (form "C" contacts). • Battery presence supervision (form "C" contacts). • AC input and DC output LED indicators. • Enclosure: <ul style="list-style-type: none"> - Combination knockouts re 1/2" and 3/4" - Accommodates up to two (2) 12VDC/7AH batteries. • Product weight: <ul style="list-style-type: none"> - AL400ULPD8: 7.6 lbs. - AL400ULPD8CB: 7.6 lbs. • Shipping weight: <ul style="list-style-type: none"> - AL400ULPD8: 8.5 lbs. - AL400ULPD8CB: 8.5 lbs. |
|--|---|

Agency Approvals



- | | |
|---------|---|
| UL 294 | UL Listed for Access Control System Units. |
| UL 603 | UL Listed Standard for Power Supplies for Use with Burglar-Alarm Systems. |
| UL 1069 | UL Listed Hospital Signaling and Nurse Call Equipment. |
| UL 1481 | UL Listed Standard for Safety for Fire Protective Signaling Systems. |



- | |
|---|
| CUL Listed - CSA Standard C22.2 No.205-M1983, Signal Equipment. |
|---|

Enclosure Dimensions

13"H x 13.5"W x 3.25"D

