

Overview



Maximal7

This unit distributes and switches power to access control systems and accessories. They convert a 115VAC 60Hz input into sixteen (16) independently controlled 24VDC fuse protected outputs. These Fail-Safe/Fail-Secure power outputs may be converted to dry form “C” contacts. The outputs are activated by an open collector sink or normally open (NO) dry trigger input from an Access Control System, Keypad, Push Button, REX PIR, etc. Units will route power to a variety of access control hardware devices including: Mag Locks, Electric Strikes, Magnetic Door Holders, etc. The FACP Interface enables Emergency Egress, Alarm Monitoring, or may be used to trigger other auxiliary devices. The fire alarm disconnect feature is individually selectable for any or all of the sixteen (16) outputs. All interconnecting equipment must be UL Listed.

Specifications

- 24VDC outputs.
- Maximum output current: 24VDC @ 9.4 amp.
- 115VAC 60Hz, 6.5 amp input.
- Input fuse rated @ 10 amp/250V.
- Power supply input options:
 - a) Two (2) common power input for either ACM8 and lock power (factory installed).
 - b) Two (2) isolated power inputs (external power supply is required), (current is determined by the power supply connected, not to exceed a maximum of 10 amp total).
- Sixteen (16) Access Control System trigger inputs. Input options:
 - a) Sixteen (16) normally open (NO) inputs.
 - b) Sixteen (16) open collector inputs.
 - c) Any combination of the above.
- Sixteen (16) independently controlled outputs. Output options:
 - a) Sixteen (16) Fail-Safe and/or Fail-Secure power outputs.
 - b) Sixteen (16) form “C” 5 amp rated relay outputs.
 - c) Any combination of the above.
- Sixteen (16) auxiliary power outputs (unswitched) (outputs are rated 2.5 amp).
- ACM8 boards main fuse is rated at 10 amp. Output fuses are rated @ 3.5 amp.
- Red LEDs indicate outputs are triggered (relays energized).
- Fire Alarm disconnect (latching or non-latching) is individually selectable for any or all of the sixteen (16) outputs.
- Fire Alarm disconnect input options:
 - a) Normally open (NO) or normally closed (NC) dry contact input.
 - b) Polarity reversal input from FACP signaling circuit.
- Alarm output relay indicates that FACP input is triggered (form “C” contact rated @ 1 amp 28VDC).
- Green LED indicates FACP disconnect is triggered.
- Filtered and electronically regulated outputs (built-in power supply).
- Built-in charger for sealed lead acid or gel type batteries.
- Maximum charge current 3.6 amp.
- Automatic switch over to stand-by battery when AC fails.
- Zero voltage drop when unit switches over to battery backup (AC failure condition).
- Thermal and short circuit protection with auto reset.
- AC input and DC output LED indicators.
- AC fail supervision (form “C” contact).
- Low battery and battery presence supervision (form “C” contact).
- Enclosure accommodates up to four (4) 12AH batteries.
- Operating temperature: 0° C to 49° C ambient.
- 64 BTU/Hr.
- Product weight (approx.): 39.2 lbs. (17.78 kg.)
- Shipping weight (approx.): 43.2 lbs. (19.6 kg.)

Agency Approvals



UL Listed for Access Control System Units
(UL 294).



CUL Listed - CSA Standard C22.2
No.205-M1983, Signal Equipment.



CSFM
California State Fire Marshal Approved.

Enclosure Dimensions (H x W x D) (approximate):

26" (660.4mm) x 19" (482.6mm) x 6.25" (158.75mm)

