



SMP10PMC12X

Overview

This power supply/charger will convert a 115VAC / 60Hz input, into a regulated 12VDC output @ 10 amp continuous supply current (see specifications).

Specifications

- | | |
|--|--|
| <ul style="list-style-type: none">• 12VDC outputs.• 10 amp supply current.• Input 115VAC @ 1.45 amp.• Filtered and electronically regulated outputs.• Short circuit and thermal overload protection.• Built-in charger for sealed lead acid or gel type batteries.• Maximum charge current .7 amp.• Automatic switch over to stand-by battery when AC fails (zero voltage drop).• AC fail supervision (form “C” contacts). | <ul style="list-style-type: none">• Low battery supervision (form “C” contacts).• Power ON/OFF switch.• AC input and DC output LED indicators.• Power supply, enclosure, cam lock & battery leads.• Enclosure:<ul style="list-style-type: none">- Combination knockouts are 1/2” and 3/4”- Accommodates up to two (2) 12VDC/7AH batteries. <p><i>SMP10PMC12X weights (approximate):</i>
Product weight: 8.4 lbs.
Shipping weight: 9.4 lbs.</p> |
|--|--|

Enclosure Dimensions

13.5"H x 13"W x 3.25"D

