



### **Overview**



- This power supply/charger converts a low voltage AC input into 6VDC, 12VDC or 24VDC @ 4 amp continuous supply current.

This unit has a wide range of applications for access control, security and CCTV system accessories that require additional power.

### **Specifications**

- |   |  |
|---|--|
| <ul style="list-style-type: none"><li>• 6VDC, 12VDC or 24VDC selectable output.</li><li>• 4 amp supply current.</li><li>• Input - Altronix transformers:<br/>For 6VDC applications use TP1640.<br/>For 12VDC or 24VDC applications use T2885.</li><li>• Filtered and electronically regulated output.</li><li>• Short circuit and thermal overload protection.</li><li>• Battery short circuit protection (circuit breaker).</li><li>• Built-in charger for sealed lead acid or gel type batteries.</li></ul> | <ul style="list-style-type: none"><li>• Maximum charge current .3 amp.</li><li>• Automatic switch over to stand-by battery when AC fails.</li><li>• AC input and DC output LED indicators.</li><li>• Extremely compact design.</li><li>• Includes battery leads.</li><li>• Snap Trac compatible (order Altronix model number ST3).</li></ul> |
|---|--|

### **Board Dimensions (approximate)**

3.5"L x 2.75"W x 1.75"H

