

# OptiSheath® MultiPort Terminal

A Corning Cable  
Systems Product

## features and benefits |

<b>OptiTap® Cable Assembly connector ports for customer drop terminations</b>	Lower installation cost and faster customer connection
<b>Available stubbed or pre-terminated with OptiTip® Multi-Fiber Connector</b>	Design flexibility and inventory simplicity
<b>4- and 12-port designs supplied with universal mounting bracket</b>	No additional mounting brackets required
<b>6- and 8-port designs with integrated mounting capability</b>	
<b>Ultrasonically welded housing</b>	Eliminates water ingress potential and prevents unwanted entry in the field
<b>Factory-terminated polished connectors</b>	Eliminates loss associated with excess fusion splices
<b>4-, 6- and 8-port configurations compatible with standard 8-in pedestal</b>	Lower profile

## standards |

Designed and third-party tested to requirements of Telcordia GR-771-CORE, Issue 1

RDUP (RUS) Listed

The OptiSheath® MultiPort Terminal is designed for use in outside plant fiber access networks. This innovative terminal provides sealed environmental protection and fast, easy incremental connection of subscriber drop cables while increasing deployment velocity. Its reliability and flexibility make it the ideal choice for network access point terminals in fiber-to-the-x (FTTx) and all-fiber access network deployments.

The OptiSheath MultiPort Terminal is available in four configurations: four, six, eight and 12 OptiTap Single-Fiber Connector ports. Used in either spliced or pre-terminated applications, the integrated cable stub is available in both dielectric and toneable cable designs.

The stubbed terminal provides the ability to consolidate cable access points by routing several terminal stubs to a single splice location. This increases workforce efficiency and reduces the overall installation time required to connect customers in FTTx networks. The optional 12-fiber OptiTip Multi-Fiber Cable Assembly is designed for use with the FlexNAP™ Terminal Distribution System for quick, easy and reliable deployments.



OptiSheath MultiPort Terminals | Photo TRCLS023

# OptiSheath® MultiPort Terminal

A Corning Cable  
Systems Product



Universal Mounting Bracket, MOB-KT-UNIV-BKT  
| Photo TRCLS002



OptiTap Single-Fiber Connector | Photo COP231

## specifications |

	Dimensions (L x H x W) mm (in)	Weight kg (lb)
4-Port Terminal	274 x 66 x 73 (10.8 x 2.6 x 2.9)	0.3 (0.7)
6- and 8-Port Terminal	312 x 76 x 86 (12.3 x 3.0 x 3.4)	0.7 (1.5)
12-Port Terminal	381 x 101 x 147 (15.0 x 4.0 x 5.8)	1.1 (2.4)

## Shipping Package

	Dimensions (L x H x W) mm (in)	Weight kg (lb)*	Method
Terminal Stub Length (cable ≤ 350 ft)	152 x 762 x 762 (6 x 30 x 30)	Contact Customer Service for details	Box
Terminal Stub Length (cable > 350 ft)	846 x 846 x 178 (33 x 33 x 7)	Contact Customer Service for details	Reel

\*Cable stub is 11.7 kg (26 lb) per 1000 ft of cable.

### Typical Insertion Loss (dB)

0.15 dB typical per OptiTap® Single-Fiber Connector > 65 dB optical return loss

0.35 dB typical per OptiTap® Multi-Fiber Connector > 65 dB optical return loss

# OptiSheath® MultiPort Terminal

A Corning Cable  
Systems Product

## ordering information |

### OptiSheath® MultiPort Terminal, Stubbed

MOB	-	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	W	-	<input type="text"/>
		1	2	3	4		5				6

|1

Select number of  
OptiTap® Single-Fiber  
Connector ports.

04 = 4 ports  
06 = 6 ports  
08 = 8 ports  
12 = 12 ports

|2

Select connector type.  
44 = Single-mode SC APC  
58 = Single-mode SC UPC

|3

Select cable type.  
FD = SST flat dielectric  
drop cable  
TD = SST flat toneable  
drop cable

|4

Select cable length.  
*See Note 1.*

|5

Select unit of measure.  
F = Feet  
M = Meters

|6

Defines packaging.  
P = Individual packaging  
*See Notes 2 and 3.*

**Notes:**

1) Minimum cable length is 10 ft  
or 3 m. Additional lengths may  
be ordered in increments of 10  
and 25 ft or 5 m. For lengths  
≥ 1000 ft, see Table A. Maximum  
length is 2000 ft or 600 m.

2) Leave blank for bulk  
packaging - minimum order  
quantities will apply.

3) Shipping reel provided on  
lengths greater than 350 ft.

**Table A: Alpha Codes  
for lengths ≥ 1000 ft**

A00	=	1000
B00	=	1100
C00	=	1200
D00	=	1300
E00	=	1400
F00	=	1500
G00	=	1600
H00	=	1700
J00	=	1800
K00	=	1900
L00	=	2000

Part Number	Description	Quantity
<b>Accessories</b>		
<b>MOB-KT-UNIV-BKT</b>	Universal Mounting Bracket Pack for 4- and 12-port housing; for aerial and handhole applications, one included with each terminal	10 per pack
<b>CLEANER-PORT-OTAP</b>	OptiTap Single-Fiber Connector Cleaner	
<b>MOB-KT-AHD</b>	4-, 6- and 8-Port Mounting Bracket for aerial strand applications	
<b>MOB-KT-AHD-12</b>	12-Port Mounting Bracket for aerial strand applications	

# OptiSheath® MultiPort Terminal

A Corning Cable  
Systems Product

## ordering information |

### OptiSheath® MultiPort Terminal with OptiTip® Multi-Fiber Cable Assembly

MTB	-	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	W	-	<input type="checkbox"/>
		1		2		3		4			5
											6

**|1**  
Select number of OptiTap® Single-Fiber Connector ports.  
04 = 4 ports  
06 = 6 ports  
08 = 8 ports  
12 = 12 ports

**|2**  
Select connector type.  
44 = Single-mode SC APC  
58 = Single-mode SC UPC

**|3**  
Select cable type.  
FD = SST flat dielectric drop cable  
TD = SST flat toneable drop cable

**|4**  
Select cable length  
*See Note 1.*

**|5**  
Select unit of measure.  
F = Feet  
M = Meters

**|6**  
Defines packaging.  
P = Individual packaging  
*See Notes 2 and 3.*

*Notes:*  
1) Minimum cable length is 10 ft or 3 m. Additional lengths may be ordered in increments of 10 and 25 ft or 5 m. For lengths ≥ 1000 ft, see Table A. Maximum length is 2000 ft or 600 m.  
2) Leave blank for bulk packaging - minimum order quantities will apply.  
3) Shipping reel provided on lengths greater than 350 ft.  
4) Minimum length for toneable MTB is 20 ft.  
5) Please contact PLM for extended length offerings.

**Table A: Alpha Codes for lengths ≥ 1000 ft**

A00	=	1000
B00	=	1100
C00	=	1200
D00	=	1300
E00	=	1400
F00	=	1500
G00	=	1600
H00	=	1700
J00	=	1800
K00	=	1900
L00	=	2000

Part Number	Description	Quantity
<b>Accessories</b>		
<b>MOB-KT-UNIV-BKT</b>	Universal Mounting Bracket Pack for 4- and 12-port housing; for aerial and handhole applications, one included with each terminal	10 per pack
<b>CLEANER-PORT-OTAP</b>	OptiTap Single-Fiber Connector Cleaner	
<b>TKT-OTMT-CLN-001</b>	OptiTip Multi-Fiber Connector Cleaning Kit	
<b>TKT-OTMT-CLN-002</b>	OptiTip Multi-Fiber Connector Cleaning Tool	
<b>MOB-KT-AHD</b>	4-, 6- and 8-Port Mounting Bracket for aerial strand applications	
<b>MOB-KT-AHD-12</b>	12-Port Mounting Bracket for aerial strand applications	

Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

Corning Cable Systems reserves the right to improve, enhance and modify the features and specifications of Corning Cable Systems products without prior notification. OptiSheath, OptiTap and OptiTip are registered trademarks of Corning Cable Systems Brands, Inc. FlexNAP is a trademark of Corning Cable Systems Brands, Inc. All other trademarks are the properties of their respective owners. Corning Cable Systems is ISO 9001 certified. © 2007, 2012 Corning Cable Systems. All rights reserved. Published in the USA.  
EVO-468-EN / May 2012