

Anixter Item #: 12G-1801POS

ShawFlex Item #: ST021M180110000

300V TP0(OS)TT-01, IEEE MARINE SHIPBOARD CABLE

1PR 18AWG 7W TINNED COPPER, FR PVC Insulation , Overall Aluminium/Mylar Tape Shielding

FR PVC Jacket

Suitable for use in 75C Wet/Dry

ABS & Transport Canada approved

Specification Reference		IEEE 45	
Electrical Characteristics			
Voltage Class (volts):	300		
Max. DC Conductor Res. (ohms/Mft @25C):	7.364	(24.16 ohms/km)
Capacitance(cond to cond)(pF / ft):	43.4	(142.5 pF / mt)
Capacitance (cond to shield)(pF / ft):	81.2	(266 pF / mt)
Ampacity @ 30C (amps)*:	13		
Inductive Reactance (Ohms/1000ft):	0.040	(0.13 ohms/Km)
Characteristic Impedance (Ohms):	52.6		
Construction Specifications			
Type of Conductor Stranding:	18AWG 7W TINNED COPPER (Concentric)		
ASTM Standard (Conductor):	ASTM B8 & ASTM B33		
Diameter of Conductor (in):	0.046	(1.17 mm)
Conductor Insulation Type:	FR PVC		
Insulation Thickness (in):	0.025	(0.64 mm)
Nominal Insulated Wire Diameter (in):	0.098	(2.49 mm)
Pair Identification:	Black & White		
Pair Twists per foot:	6.00	(19.69 m)
Type of Overall Shielding Tape:	1.0" X 1.35 MIL STR-EDGE AL/MYLAR Tape		
Overall Shielding Drain Wire Size:	20 AWG 7W TINNED COPPER		
Jacket Type & Colour:	90C -40C FR PVC, BLACK		
Average Outer Jacket Thickness (in):	0.045	(1.14 mm)
Nominal Overall OD of Cable (in):	0.303	(7.7 mm)
Jacket Identification:	SHAWFLEX ST 1PR 18AWG TP0(OS)TT-01 300V (-35C) MARINE SHIPBOARD CABLE ANSI/IEEE Std 1580-2001 ETL LISTED 111525 MADE IN CANADA ST021M180110000 (mo#) (month year) (sequential metre marking every 1 metre)		
Physical Characteristics			
Cable Weight (lbs/Mft):	49	(74 kg/km)
Max. Pulling Tension (Pulling Eye) (lbs):	26	(12 kg)
Max. Pulling Tension (Cable Grip) (lbs):	36	(17 kg)
Min. Bending Radius: Permanent (in):	3.6	(92 mm)
Min. Bending Radius: Pull (in):	5.5	(139 mm)
Max. Conductor Temperature (C):	75C		
Recommended Min. Install Temp. (C):	-10C		
Copper Content(lbs/Mft):	13.4	(20.0 kg/km)
Flame Propagation Test Rating:	CSA FT-4, IEC 60332-3 Category 'A'		
Additional Ratings:	-35C Cold Impact, -40C Cold Bend		

* Ampacity value based on IEEE Standard 45, Table-9-1. Values are corrected according to Table-9-1 for number of Conductors.

This specification is issued on condition that it is not copied, reprinted or disclosed either wholly or in part to any third party, or used for manufacture by any party; without the consent of ShawFlex.