

# CPX 100

INSULATE  
SEAL  
PROTECT

2:1  
SHRINK RATIO



## THIN WALL CROSS-LINKED POLYOLEFIN

Flexible, multi-purpose heat shrink tubing

### FEATURES AND BENEFITS


- 2:1 shrink ratio
- Flame retardant (colors only)
- Resistant to common fluids and solvents
- Economical mechanical protection for terminal strain relief and wire bundling
- Continuous operating temperature: -55°C to 135°C
- Shrink temperature: 90°C

### STANDARDS

- UL 224, 125°C (colors only)
- CSA C22.2 No. 198.1, 125°C
- SAE-AMS-DTL-23053/5 Class 1 and 2
- AMS 3636 and 3637
- DEF STAN 59-97 Issue 3 Type 2a


### TYPICAL APPLICATIONS

- Electrical insulation of wire splices and terminals
- Strain relief of wire terminations
- Protects components from abrasion and fluids



DIMENSIONS

ORDER NUMBER	EXPANDED		RECOVERED				LENGTHS	
	INTERNAL DIAMETER (MIN.) D		INTERNAL DIAMETER (MAX.) d		WALL THICKNESS (NOM.) W			
	MM	IN	MM	IN	MM	IN	M	FT
0047	1.2	3/64	0.6	3/128	0.41	0.016	300	1000
0063	1.6	1/16	0.8	1/32	0.43	0.017	300	1000
0094	2.4	3/32	1.2	3/64	0.51	0.020	300	1000
0125	3.2	1/8	1.6	1/16	0.51	0.020	300	1000
0187	4.8	3/16	2.4	3/32	0.51	0.020	300	1000
0250	6.4	1/4	3.2	1/8	0.64	0.025	150	500
0375	9.5	3/8	4.7	3/16	0.64	0.025	150	500
0500	12.7	1/2	6.4	1/4	0.64	0.025	60	200
0625	16.0	5/8	8.0	5/16	0.76	0.030	60	200
0750	19.0	3/4	9.5	3/8	0.76	0.030	30	100
1000	25.4	1	12.7	1/2	0.89	0.035	30	100
1250	32.0	1 ¼	16.0	5/8	0.89	0.035	30	100
1500	38.1	1 ½	19.0	3/4	1.02	0.040	30	100
2000	50.8	2	25.4	1	1.14	0.045	30	100
3000	76.2	3	38.0	1 ½	1.27	0.050	15	50
4000	101.6	4	50.8	2	1.40	0.055	15	50



ORDERING

- Select a dimension which will shrink snugly over the component to be covered. If recovery is restricted the resultant wall thickness will be less than specified.
- Select options:
  - Colour: Black (BK), Red (RD), White (WT), Clear (CL), Blue (BL), Yellow (YL), Green (GR)
  - Length: Standard Stick, Spool or custom length
- Please specify the product name, order reference number and options you require
- Order Example: CPX 100, 0375, black, 500 ft

Please contact your Customer Service Representative for information on custom colours, sizes, lengths and material data sheet.

All information contained in this data sheet is believed to be reliable. We advise, however, that customers should separately evaluate the suitability of our products for their particular application. DSG-Canada and ShawCor give no guarantees in respect of the accuracy or sufficiency of the information presented and disclaim any liability regarding its use. Our responsibilities are only those listed in our Standard Terms and Conditions of Sale for these products. In no instance will we be liable for any eventual, indirect or consequential damage or damages arising from the sale, resale, transfer, use or misuse of the product.