



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TLP606

### 6-outlet, 6-ft cord, 790 joule strip - Protect It! Surge Suppressor



#### Highlights

- 6 outlet / 6-ft. cord
- 790 joule rating
- \$20,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

#### Description

Tripp Lite's TLP606 offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP606 offers 6 total outlets, 6 foot cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 790 joules shields equipment from surges and line noise. Attractive white suppressor housing with keyhole mounting tabs offer convenient protection of desktop computer equipment and accessories. \$20,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/790 joules/400V UL1449 3rd Edition

#### Applications

- Ideal for any desktop, network or home computing application requiring AC line protection

#### Package Includes

- TLP606 surge suppressor
- Instruction manual with warranty information

#### Features

- 6 outlets
- 6-ft. cord
- Surge suppression rating: 790 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Green protection LED
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate 1 large transformer plug without covering remaining outlets, 3 total transformers
- Keyhole support for wall mounting
- Lighted power switch
- \$20,000 Ultimate Lifetime Insurance (USA and Canada Only)

#### Specifications

##### OVERVIEW

Intended Application	Home/Office
<b>OUTPUT</b>	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Overload protection	15A resettable illuminated combo switch / circuit breaker
Outlet quantity / type	6 NEMA 5-15R
Transformer accommodation	Supports 1 large transformer plug accessory without covering remaining outlets, accepts up to 3 transformers total
Outlet orientation	Single row of 6 outlets
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length (ft.)	6
Input cord length (m)	1.83
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	35500
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	790
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	400V
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping weight (lbs)	1.20
Shipping weight (kg)	0.53

<b>Unit Dimensions (HWD/in)</b>	10.8 x 1.85 x 1.23
<b>Unit Dimensions (HWD/cm)</b>	3.20 x 4.19 x 26.29
<b>Shipping Dimensions (HWD/in)</b>	13.2 x 5 x 1.80
<b>Shipping Dimensions (HWD/cm)</b>	30.99 x 11.99 x 3.78
<b>Unit weight (lbs)</b>	1.01
<b>Unit weight (kg)</b>	0.48
<b>Material of construction</b>	Plastic
<b>Integrated keyhole mounting tabs</b>	Keyhole mounting tabs enable wall mounting
<b>Housing Color</b>	Light Gray
<b>Receptacle Color</b>	Light Gray
<b>AC line cord color</b>	Light Gray
<b>Style</b>	Strip
<b>Outlets center to center measurement</b>	28.5mm
<b>Keyhole slot center to center measurement</b>	Distance between slots = 101mm; Distance between slot height = 28mm
<b>CERTIFICATIONS</b>	
<b>UL1449 3rd Edition (AC Suppression)</b>	UL1449 3rd EDITION
<b>UL1363 (Power Tap)</b>	UL1363
<b>cUL / CSA (Canada)</b>	cUL
<b>Approvals</b>	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
<b>Product Warranty Period (Worldwide)</b>	Lifetime limited warranty
<b>Connected Equipment Insurance (U.S., Canada &amp; Puerto Rico)</b>	\$20,000 <a href="#">Ultimate Lifetime Insurance</a>

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2632](http://www.tripplite.com/en/products/model.cfm?txtModelID=2632).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.