


Product Data Sheet

3266 (0.016 in. Wall, 300 V)



Product Description

Irradiated XLPE
Stranded and solid conductor
UL AWM
CSA AWM

Applications

Internal wiring of computers, test equipment, and other office and control equipment.

Specifications

- CONDUCTOR: Tinned copper
- INSULATION: Cross-Linked Polyethylene (XLPE), irradiated
- STANDARDS: Complies with MIL-Spec 16878/15. UL recognized AWM Style 3266 per UL 758 requirements
- TEMPERATURE: -55 °C to 125 °C
- VOLTAGE: 300 V

Product Data Sheet

All part numbers require color code designation. Diameters and weights may vary among manufacturers.

Part No.	Conductor AWG	Stranding No. x AWG	Conductor Nom. Dia.	Wire O.D.	Approx. Wt. lb./1,000 ft.
3266-26/1-XX	26	Solid	0.016	0.048	1.8
3266-26/7-XX	26	7x34	0.019	0.051	2.0
3266-24/1-XX	24	Solid	0.020	0.052	2.4
3266-24/7-XX	24	7x32	0.024	0.056	2.8
3266-22/7-XX	22	7x30	0.030	0.062	3.7
3266-20/1-XX	20	Solid	0.032	0.064	4.6
3266-20/7-XX	20	7x28	0.038	0.070	4.8
3266-18/7-XX	18	7x26	0.048	0.080	7.0
3266-18/19-XX	18	19x30	0.047	0.079	7.0
3266-16/19-XX	16	19x29	0.053	0.089	10.3
3266-16/26-XX	16	26x30	0.060	0.092	10.5
3266-14/19-XX	14	19x27	0.067	0.106	15.6
3266-12/19-XX	12	19x25	0.084	0.127	24.7
3266-10/37-XX	10	37x26	0.110	0.154	37.2