

# Product Data Sheet

High definition coax for SDI, digital video, and precision analog video applications.

## Product Description

High definition coax for SDI, digital video, and precision analog video applications.

## Specifications

- CONDUCTOR: Solid bare copper
- SHIELDING: Foil tape + 95% tinned copper braid
- INSULATION: Foam-Fluorinated ethylene-propylene (FFEP)
- JACKET: Polyvinyl Chloride (PVC)
- IMPEDANCE: 75 OHM
- NEC: CMR or CL3R
- RATINGS: 75C, 300V

Part No.	Description	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.
AV-HDRG11R	RG11 14 AWG solid bare copper, foil tape, 95% tinned copper braid, black PVC jacket.	0.272	82
AV-HDRG59R	RG59 20 AWG solid bare copper, foil tape, 95% tinned copper braid, black PVC jacket.	0.233	29
AV-HDRG59R-MINI	RG59 23 AWG solid bare copper, foil tape, 95% tinned copper braid, black PVC jacket.	0.159	14
AV-HDRG6R	RG6 18 AWG solid bare copper, foil tape, 95% tinned copper braid, black PVC jacket.	0.272	39