








M 4/6.T	M 4/6.1	M 4/6.2	M 4/6.3	M 4/6.4	M 4/6.C	D 4/6
Spacing 6 mm + 0,05 (.238")	Spacing 6 mm + 0,05 (.238")	Spacing 6 mm + 0,05 (.238")	Spacing 6 mm + 0,05 (.238")	Spacing 6 mm + 0,05 (.238")	Spacing 6 mm + 0,05 (.238")	Spacing 6 mm + 0,05 (.238")
						
Grey  0115 224.13 Beige V0  0195 224.14 M 4/6 with 1 test socket screw DIA. 2 mm/.079" on the right	Grey  0115 259.06 Beige V0  0195 259.07 M 4/6 with partition	Grey  0115 217.14 Beige V0  0195 217.15 M 4/6.1 equipped with a test socket DIA. 2 mm/.079"	Grey  0115 268.07 Beige V0  0195 268.00 M 4/6.1 equipped with a test socket DIA. 3 mm/.12"	Grey  0115 192.04 Beige V0  0195 192.05 M 4/6.1 equipped with a test socket DIA. 4 mm/.16"	Grey  0115 208.04 Beige V0  0195 208.05 M 4/6.1 equipped with a test socket DIA. 2,5 mm/.10" for connector	Grey  0215 116.13 M 4/6 without central foot for DIN 3 rail only
						
Part numbers	Part numbers	Part numbers	Part numbers	Part numbers	Part numbers	Part numbers
0118 368.16	0118 368.16	0118 368.16	0118 368.16	0118 368.16	0118 368.16	0118 368.16
0128 368.10	0128 368.10	0128 368.10	0128 368.10	0128 368.10	0128 368.10	0128 368.10
0103 126.16	0103 126.16	0103 126.16	0103 126.16	0103 126.16	0103 126.16	0103 126.16
0103 062.21	0103 062.21	0103 062.21	0103 062.21	0103 062.21	0103 062.21	0103 062.21
0103 125.15	0103 125.15	0103 125.15	0103 125.15	0103 125.15	0103 125.15	0103 125.15
0103 312.20	0103 312.20	0103 312.20	0103 312.20	0103 312.20	0103 312.20	0103 312.20
V0 0198 368.17	V0 0198 368.17	V0 0198 368.17	V0 0198 368.17	V0 0198 368.17	V0 0198 368.17	V0 0198 368.17
V0 0199 302.07	V0 0199 302.07	V0 0199 302.07	V0 0199 302.07	V0 0199 302.07	V0 0199 302.07	V0 0199 302.07
V0 0199 305.02	V0 0199 305.02	V0 0199 305.02	V0 0199 305.02	V0 0199 305.02	V0 0199 305.02	V0 0199 305.02
(3) 0114 776.23	(3) 0114 776.23	(3) 0114 776.23	(3) 0114 776.23	(3) 0114 776.23	(3) 0114 776.23	
(3) 0114 777.24	(3) 0114 777.24	(3) 0114 777.24	(3) 0114 777.24	(3) 0114 777.24	(3) 0114 777.24	
0113 003.10	0113 003.10	0113 003.10	0113 003.10	0113 003.10	0113 003.10	0113 003.10
0123 003.12	0123 003.12	0123 003.12	0123 003.12	0123 003.12	0123 003.12	0123 003.12
V0 0193 003.11	V0 0193 003.11	V0 0193 003.11	V0 0193 003.11	V0 0193 003.11	V0 0193 003.11	V0 0193 003.11
0118 707.03	0118 707.03	0118 707.03	0118 707.03	0118 707.03	0118 707.03	0118 707.03
0128 707.05	0128 707.05	0128 707.05	0128 707.05	0128 707.05	0128 707.05	0128 707.05
V0 0198 707.04	V0 0198 707.04	V0 0198 707.04	V0 0198 707.04	V0 0198 707.04	V0 0198 707.04	V0 0198 707.04
0114 202.25	0114 202.25	0114 202.25	0114 202.25	0114 202.25	0114 202.25	0114 202.25
(3) 0114 825.05	(3) 0114 825.05	(3) 0114 825.05	(3) 0114 825.05	(3) 0114 825.05	(3) 0114 825.05	
(3) 0103 619.04	(3) 0103 619.04	(3) 0103 619.04	(3) 0103 619.04	(3) 0103 619.04	(3) 0103 619.04	
(3) 0103 620.01	(3) 0103 620.01	(3) 0103 620.01	(3) 0103 620.01	(3) 0103 620.01	(3) 0103 620.01	(3) 0103 620.01
(3) 0116 795.11	(3) 0116 795.11	(3) 0116 795.11	(3) 0116 795.11	(3) 0116 795.11	(3) 0116 795.11	(3) 0116 795.11
(3)V0 0196 795.12	(3)V0 0196 795.12	(3)V0 0196 795.12	(3)V0 0196 795.12	(3)V0 0196 795.12	(3)V0 0196 795.12	(3)V0 0196 795.12
0187 312.14	0187 312.14	0187 312.14	0187 312.14	0187 312.14	0187 312.14	0187 312.14
0176 816.12	0176 816.12	0176 816.12	0176 816.12	0176 816.12	0176 816.12	0176 816.12
	0163 043.21					(1) 0163 043.21
	0163 261.00					(1) 0163 261.00
	0173 059.03					0173 059.03
0007 865.26	0007 865.26	0007 865.26			0007 865.26	0007 865.26
				0167 860.01		0167 860.01
(1) 0168 516.25	(5) 0168 516.25					(1) 0168 516.25
(1) 0168 517.26	(5) 0168 517.26					(1) 0168 517.26
(1) 0168 518.07	(5) 0168 518.07					(1) 0168 518.07
(1) 0168 519.00	(5) 0168 519.00					(1) 0168 519.00
(1) 0168 973.07	(5) 0168 973.07					(1) 0168 973.07
(1) 0176 663.00	(5) 0176 663.00					(1) 0176 663.00
(1) 0176 664.01	(5) 0176 664.01					(1) 0176 664.01
(1) 0176 665.02	(5) 0176 665.02					(1) 0176 665.02
(1) 0176 666.03	(5) 0176 666.03					(1) 0176 666.03
(1) 0176 667.04	(5) 0176 667.04					(1) 0176 667.04
(1) 0174 784.20	(5) 0174 784.20					(1) 0174 784.20
0168 604.16	0168 604.16					0168 604.16
0173 627.21	0173 627.21	0173 627.21	0173 627.21	0173 627.21	0173 627.21	0173 627.21
0299 694.04	0299 694.04	0299 694.04	0299 694.04	0299 694.04	0299 694.04	(4) 0299 694.04
0299 695.05	0299 695.05	0299 695.05	0299 695.05	0299 695.05	0299 695.05	(4) 0299 695.05
0299 696.06	0299 696.06	0299 696.06	0299 696.06	0299 696.06	0299 696.06	(4) 0299 696.06
0299 697.07	0299 697.07	0299 697.07	0299 697.07	0299 697.07	0299 697.07	(4) 0299 697.07
0299 702.14	0299 702.14	0299 702.14	0299 702.14	0299 702.14	0299 702.14	(4) 0299 702.14
0199 466.23	0199 466.23	0199 466.23	0199 466.23	0199 466.23	0199 466.23	0199 466.23
(1) 0174 413.14	(5) 0174 413.14					(1) 0174 413.14
(1) 0116 541.12	(5) 0116 541.12					(1) 0116 541.12
(1)(2) 0179 623.03	(2)(5) 0179 623.03					(1)(2) 0179 623.03
(1)(2) 0179 625.05	(2)(5) 0179 625.05					(1)(2) 0179 625.05
(1)(2) 0174 781.25	(2)(5) 0174 781.25					(1)(2) 0174 781.25
0113 546.14	0113 546.14	0113 546.14	0113 546.14	0113 546.14	0113 546.14	(4) 0113 546.14
0113 548.26	0113 548.26	0113 548.26	0113 548.26	0113 548.26	0113 548.26	(4) 0113 548.26
0113 550.24	0113 550.24	0113 550.24	0113 550.24	0113 550.24	0113 550.24	0113 550.24
0178 745.14	0178 745.14	0178 745.14	0178 745.14	0178 745.14	0178 745.14	0178 745.14
0178 746.15	0178 746.15	0178 746.15	0178 746.15	0178 746.15	0178 746.15	0178 746.15
0163 427.17	0163 427.17					0163 427.17
0163 433.15	0163 433.15					0163 433.15
0107 038.25	0107 038.25	0107 038.25	0107 038.25	0107 038.25	0107 038.25	0107 038.25
0114 205.20	0114 205.20	0114 205.20	0114 205.20	0114 205.20	0114 205.20	0114 205.20
(11) (12)	(11) (12) (5)	(11)	(11)	(11)	(11)	(11) (12)

Note : (1) A circuit separator SC may be required with the use of these accessories. (2) See "Notes". (3) End sections and separators snapped on rails. (5) Use of these accessories requires the user to cut out the partition.

R See section on markers method (11) (12)

Note: (1) A circuit separator SC may be required with the use of these accessories.
(2) See "Notes". (3) End sections and separators snapped on rails.
(4) See section: "Accessories" for other configurations of poles.

FEM6		th.	2,8 mm	0118 368.16
FEM6		th.	2,8 mm	0128 368.10
FEM6		th.	2,8 mm	0103 126.16
FEM6		th.	2,8 mm	0103 062.21
FEM6		th.	2,8 mm	0103 125.15
FEM6		th.	2,8 mm	0103 312.20
FEM6 V0	V0	th.	2,8 mm	0198 368.17
FEM6 V0	V0	th.	2,8 mm	0199 302.07
FEM6 V0	V0	th.	2,8 mm	0199 305.02
FEM61	(3)	th.	3,0 mm	0114 776.23
FEM6C	(3)	th.	3,0 mm	0114 777.24
SCM6				0113 003.10
SCM6				0123 003.12
SCM6 V0	V0			0193 003.11
SCF6		th.	3,0 mm	0118 707.03
SCF6		th.	3,0 mm	0128 707.05
SCF6 V0	V0	th.	3,0 mm	0198 707.04
SCF61		th.	3,0 mm	0114 202.25
SCFM6	(3)	th.	3,0 mm	0114 825.05
SCFEX1	(3) 	th.	2,4 mm	0103 619.04
SCFCX3	(3) 	th.	2,4 mm	0103 620.01
SCFCV1-2	(3)	th.	3,0 mm	0116 795.11
SCFCV1-2 V0(3)V0		th.	3,0 mm	0196 795.12
CPM	(for FEM6C, SCF6(V0) and SCFM6)			0187 312.14
CPV1-2	(for SCFCV1-2...)			0176 816.12
AL2	(1)	DIA.	2 mm	0163 043.21
AL3	(1)	DIA.	3 mm	0163 261.00
DCJ			yellow	0173 059.03
FC2		DIA.	2 mm	0007 865.26
FC4		DIA.	4 mm	0167 860.01
BJM6	(1)	2	poles	0168 516.25
BJM6	(1)	3	poles	0168 517.26
BJM6	(1)	4	poles	0168 518.07
BJM6	(1)	5	poles	0168 519.00
BJM6	(1)	10	poles	0168 973.07
BJM16	(1)	2	poles	0176 663.00
BJM16	(1)	3	poles	0176 664.01
BJM16	(1)	4	poles	0176 665.02
BJM16	(1)	5	poles	0176 666.03
BJM16	(1)	10	poles	0176 667.04
BJS6	(1)	20	poles	0174 784.20
EV6				0168 604.16
EL6				0173 627.21
BJE6.2	(4)	2	poles	0299 694.04
BJE6.3	(4)	3	poles	0299 695.05
BJE6.4	(4)	4	poles	0299 696.06
BJE6.5	(4)	5	poles	0299 697.07
BJE6.10	(4)	10	poles	0299 702.14
BJB				0199 466.23
BJP6	(1)			0174 413.14
BJA6	(1)	10	poles	0116 541.12
BJDP1	(1)(2) spacing 6 <=> spacing 16			0179 623.03
BJDP3	(1)(2) spacing 6 <=> spacing 12			0179 625.05
BJDP4	(1)(2) spacing 6 <=> spacing 8 or 10			0174 781.25
PC6	(4)	2	poles	0113 546.14
PC6	(4)	10	poles	0113 548.26
EIP				0113 550.24
CBM5		th.	0,5 mm	0178 745.14
CBM8		th.	0,8 mm	0178 746.15
EP6		4	blocks	0163 427.17
VSP6				0163 433.15
EPU6				0107 038.25
AD2.5				0114 205.20