



Han® PushPull, type acc. to IEC 61 076-3-118  
Housing bulkhead mounting and power females for device integration

## Features

- HARTING PushPull technology
- Compact, space-saving design
- Touch-proof
- Device side: male
  - Solder variant, angled and straight
- 4 times coding without contact loss

## Technical characteristics

|                                       |  |
|---------------------------------------|--|
| Locking                               | PushPull technology acc. to IEC 61 076-3-118 |
| Degree of protection                  | IP 65 / IP 67                                |
| Number of contacts                    | 4 + PE                                       |
| Electrical data acc. to DIN EN 61 984 | 16 A 230/400 V 4 kV 3                        |
| Termination                           | Male insert with solder termination          |
| Mating cycles                         | min. 500                                     |
| Temperature range                     | -40 °C ... +70 °C                            |
| Housing material                      | Plastic, black                               |
| Flammability acc. to UL 94            | V 0  |

| Identification | Part No. | Drawing | Dimensions in mm |
|----------------|----------|---------|------------------|
|----------------|----------|---------|------------------|

### Components device side

|  |                |  |  |
|--|----------------|--|--|
| Housing bulkhead mounting plastic            | 09 35 002 0323 |  |  |
| Dust protection cover IP 40, rubber (NBR)    | 09 35 002 5401 |  |  |
| Protection cover IP 65 / IP 67               | 09 35 002 5402 |  |  |
| Coding pins                                  | 09 35 000 6190 |  |  |
| Male insert with solder termination angled   | 09 35 002 3003 |  |  |
| Male insert with solder termination straight | 09 35 002 3004 |  |  |

