



HARTING PushPull Power 2/0, type acc. to IEC 61076-3-106 variant 4 panel feed-through and connector, 3-poles, 250 V / 16 A

Advantages

- Power connectors for devices
- EasyInstall panel feed-through for simple device integration
- Compact, space-saving design
- Touch-proof according to IEC DIN EN 60 529
- Polarisation with nose
- Cable side: Male with crimp termination
- Device side: female with crimp termination
- 4 different coding variants without loss of contact

Technical characteristics

| | |
|--------------------------------------|---|
| Locking | PushPull Technology acc. to IEC 61 076-3-106 variant 4 |
| Degree of protection | IP 65 / IP 67 |
| Number of contacts | 2 + PE |
| Electrical data acc. to EN 61 984 | 16 A 250 V 4 kV 3 |
| Cable diameter | 4.9 ... 8.6 mm |
| Termination | Crimp |
| Termination cross section | 0.75 - 2.5 mm ² (AWG 20 - 12) stranded |
| Mating cycles | min. 750 |
| Temperature range | -40 °C ... +70 °C |
| Housing material | Plastic, black |
| Flammability acc. to UL 94 | V 0 |

| Identification | Part No. | Drawing | Dimensions in mm |
|---|----------------|---------|------------------|
| HARTING PushPull Power 2/0 Panel feed-through set incl. 3 turned crimp contacts (female) for 1.5 mm ² , insulation body (black), housing bulkhead mounting EasyInstall | 09 46 245 3430 | | |
| Panel feed-through set incl. 3 turned contacts (female) for 1.5 mm ² , insulation body (black), housing bulkhead mounting, with crimp termination | 09 46 245 3410 | | |
| Power-female with crimp termination without contacts | 09 46 500 3401 | | |
| Connector set incl. 3 turned crimp contacts (male) for 1.5 mm ² , insulation body (black), housing, cable gland | 09 46 145 3410 | | |
| Connector set without contacts | 09 46 145 3411 | | |
| Coding pin set to avoid accidental incorrect mating a coding system is required. This coding pins are inserted without loss of contact. | 09 46 840 0000 | | |