



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: PDU3VSR10G60

**3-Phase Switched PDU, 12.6 kW, 24 208V outlets (21-C13, 3-C19) 10-ft. Cord, IEC-309 Blue 60A input, 0U vertical mount**



### Highlights

- Switched 12.6kW 3 Phase 208V PDU; 70 in. / 178cm 0U vertical rackmount
- Reports voltage, frequency & load per-outlet or phase via ethernet interface
- Visual current meter; Toolless button-mount installation
- IEC-309 Blue 60A (3P+E) 208V 3 phase input; 10 ft. / 3m line cord
- 21 C13 & 3 C19 single phase switched outlets with cord retention brackets
- Temperature, humidity and contact closure monitoring options

### Description

Tripp Lite 3 phase Switched PDU / Power Distribution Unit offers advanced network control and monitoring with the ability to turn on, turn off, recycle or lock-out power to each individual receptacle, monitor site electrical conditions and remotely monitor output power consumption per-phase or per-receptacle. PowerAlert interface supports remote control and custom notification of user-specified conditions via email, secure web, SNMP, Telnet or SSH interface. Individually switched outlets can be controlled in real-time to remotely reboot unresponsive network hardware, or be custom programmed for user-defined power-up and power-down sequences to ensure proper startup of interdependent IT systems and prevent inrush-related overloads as network equipment is first energized. Unused PDU outlets can be electronically locked off to prevent the connection of unauthorized hardware. PDU output current consumption in amps per-phase or per-receptacle can be displayed locally via visual meter or remotely via web/network interface to warn of potential overloads before critical IT mains or branch breakers trip.

#### Applications

- Ideal for 3 phase network configurations in datacenters and heavily configured equipment racks

#### Package Includes

- Switched rackmount PDU with pre-installed mounting buttons
- Cord retention brackets
- Rack mounting brackets
- Owner's manual

### Features

- 12.6kW 3 phase 208V Switched Power Distribution Unit / PDU with built-in web/network interface
- Attached IEC-309 Blue 60A (3P+E) 208V 3 phase input; 10 ft. / 3m cord
- 0U, 70 inch / 178cm vertical form factor
- 24 switched 208V outlets (21 C13, 3 C19) in 3 single phase load banks
- Supports power-on, power-off or reboot of each outlet on a real-time or programmable basis
- Enables reboot of locked equipment, custom power-on/power-off sequences, load-shedding of optional loads and disabling unused outlets
- Network interface provides PDU control and data regarding input voltage, per-outlet and per-phase load levels
- Digital display with scroll-buttons supports per-outlet or per-phase load levels, IP-address self-identification and 180 degree display rotation
- Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH door sensors
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing

- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Included cord retention brackets
- Toolless mounting in button-mount compatible racks
- Nut-and-bolt mounting support for other racks

## Specifications

OVERVIEW	
PDU Type	Switched
OUTPUT	
Output Capacity Details	12.6kVA total; 20A per bank (balanced)
Frequency compatibility	60 Hz
Output nominal voltage	208V single phase
Overload protection	3 20A double-pole circuit breakers (1 per output phase)
Outlet quantity / type	24 total - 21 C13 (7 per phase), 3 C19 (1 per phase)
Outlet Type	IEC-C13, IEC-C19
Customized load management receptacles	Each outlet is individually controllable via remote interface
INPUT	
Nominal Input Voltage(s) Supported	208V AC
PDU Input Voltage	208
Recommended Electrical Service	208V 3 phase
Maximum Input Amps (A)	35
Input connection type	IEC-309 Blue 60A (3P+E)
Plug Type	IEC-309 Blue 60A (3P+E)
PDU Plug Type	IEC-309 60A BLUE (3P+E)
Input cord length (ft.)	10
Input cord length (m)	3.05
Voltage compatibility (VAC)	3-Phase; 208
Phase	3-Phase
LEDS ALARMS & SWITCHES	
Switches	Pushbutton scroll switch enables local power consumption display of each phase or outlet separately, display rotate and display IP address functions
Front panel LEDs	2 digit current meter display reports output amps per phase and IP address self identification
PHYSICAL	

Shipping weight (lbs)	20.45
Shipping weight (kg)	9.3
Unit Dimensions (HWD/in)	70 x 2.19 x 3.26
Unit Dimensions (HWD/cm)	177.8 x 5.6 x 8.3
Shipping Dimensions (HWD/in)	75.4 x 6.6 x 9.3
Shipping Dimensions (HWD/cm)	191.5 x 16.8 x 23.6
Unit weight (lbs)	13.2
Unit weight (kg)	6
Material of construction	Steel
Style	Vertical rackmount
Form factors supported	Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks
PDU Form Factor	Vertical (0U)
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% non-condensing
<b>COMMUNICATIONS</b>	
SNMP compatibility	Yes, pre-installed <a href="#">SNMPWEBCARD</a> provides remote monitoring via web, telnet, SSH and SNMP management systems
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL 60950-1 (USA, Canada), Class A (Emissions), NOM (Mexico), RoHS compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

## Related Items

### Optional Products

Related Model	Description	Qty.
<a href="#">P002-002</a>	2-ft. Power Cord (IEC-320-C14 to NEMA 5-15R)	1
<a href="#">P005-002</a>	2-ft. Heavy-Duty 14AWG Power cord ( IEC-320-C13 to IEC-320-C14)	1
<a href="#">P005-006</a>	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14)	1
<a href="#">P005-010</a>	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14)	1
<a href="#">P047-002</a>	2-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
<a href="#">P047-004</a>	4-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
<a href="#">P047-006</a>	6-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1

P047-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
P032-007	7-ft. 12AWG Heavy Duty Power cord ( IEC-320- C13 to IEC-320-C20)	1
P036-002	2-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20)	1
P036-006	6-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20)	1
ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
SRSWITCH	Rack door sensor (4 max.); Requires ENVIROSENSE	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=4588](http://www.tripplite.com/en/products/model.cfm?txtModelID=4588).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.