



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SMX1500XLRT2U

SmartPro 1.5kVA Line Interactive Sine Wave UPS, Extended-run & SNMPWEBCARD options, 2U Rack/Tower, USB, Serial, EPO, 230V

Highlights



- 1500VA / 1.5kVA line interactive 2U rack / tower UPS; Sine wave output
- 230V nominal output during brownouts to 151V and overvoltages to 282V
- USB, RS232, EPO and optional SNMP/Web card interface
- Expandable runtime, Status LEDs with load and battery capacity display
- 3 independently switchable output load banks; 13.5 in / 34.3 cm depth
- C14 input; 8 C13 outlets; Includes 2 C13 to C14 cables

Description

Tripp Lite's SMX1500XLRT2U intelligent, line interactive rack/tower uninterruptible power supply prevents data loss, downtime and equipment damage due to power outages, voltage fluctuations and transient surges. Requires only two rack spaces (2U) in a standard rack enclosure. Large internal batteries offer 18 minutes half load runtime and 7 minutes at full load. Runtime is expandable with optional BP36V15-2U external battery pack (limit 1) or BP36V42-3U (multi-pack compatible). Maintains regulated 230V nominal output without using battery power during brownouts and overvoltages from 151 to 282V. 1500VA/1000 watt power handling capability and full time sine wave output offers guaranteed compatibility with networking, telecom and other sensitive electronic applications. Includes a total of 8 outlets with 3 load banks that are individually switchable via software interface to reboot select equipment on demand or shed less significant loads to extend battery runtime for more critical equipment. Supports simultaneous remote monitoring of UPS and site power conditions via built-in USB and DB9 monitoring ports. Includes PowerAlert UPS monitoring and unattended shutdown software with complete cabling. Built-in accessory slot supports SNMP with optional SNMPWEBCARD adapter. Emergency Power Off (EPO) interface offers option for instantaneous power-off of UPS and connected equipment in the case of fire or emergency. Multi-function audible alarms and set of 5 front panel LEDs offer at-a-glance notification of UPS and line power status. Network-grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges and line noise. Attractive all-black color scheme.

Package Includes

- SMX1500XLRT2U UPS System with mounting hardware
- Two 1.8m IEC320-C13 to C14 load jumper cables
- Cabling for USB & DB9 monitoring and EPO switching
- PowerAlert unattended shutdown and UPS/Power monitoring software
- Warranty information and instruction manual

Features

- SMX1500XLRT2U line interactive UPS offers battery derived sine wave AC output during power outages, voltage regulation during brownouts and overvoltages, plus network-grade AC surge suppression
- 1500VA/1000 watt power handling capability with full-time sine wave output offers guaranteed compatibility with networking, telecom and other sensitive electronic devices
- Supports 2U rackmount installation in 4 post equipment racks, 2 post rackmount installation requires 2POSTRMKITWM, upright tower

installation requires 2-9USTAND accessory

- Large internal batteries support a max load of 1500VA for 7 minutes and a half load of 750VA for 18 minutes
- Expandable runtime with BP36V15-2U (limit 1) or with multiple BP36V42-3U rack/tower external battery packs
- Maintains regulated 230V nominal output during brownouts and overvoltages from 151 to 282V
- Includes 8 UPS supported outlets arranged in 3 individually controllable load banks (2 outlets per bank) that can be powered off and back on again via software interface
- IEC320-C14 input connection accepts a variety of detachable cordsets to match country or site-specific wall receptacles
- PowerAlert UPS monitoring and unattended shutdown software enables configurable network broadcast messaging, email notification, event logging and running user-defined script commands.
- Offers simultaneous monitoring by up to 2 directly-connected devices through included USB and DB9 interface ports, or the monitoring by any number of additional servers over IP with included PowerAlert monitoring software.
- Communications ports support messaging of UPS and line power status, including on-battery, low-battery, power restored, AC line voltage, DC battery voltage and remaining battery capacity
- Emergency Power Off (EPO) interface with cable
- Supports timed inverter shutoff after unattended shutdown, activate self-test and UPS output power control for delayed or immediate reboot of connected devices
- Supports Tripp Lite's WatchDog software application to restore operation to locked equipment through soft reboot of application, OS or hard power off/on reboot of connected equipment - ideal for unattended kiosk applications (requires optional WATCHDOGSW)
- Built-in accessory slot supports SNMP with optional SNMPWEBCARD adapter
- Emergency Power Off (EPO) interface with cable
- Multi-function audible alarms and set of 5 front panel LEDs
- Network-grade AC surge suppression
- Attractive all-black color scheme
- UPS battery set ships fully assembled, no time consuming connection of internal batteries by user is necessary

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1500
Output kVA capacity (kVA)	1.5
Output Watt Capacity (watts)	1000
Output kW capacity	1
Output power factor	0.7
Nominal Output Voltage(s) Supported	230V
Nominal Voltage details	230v nominal inverter output voltage
Frequency compatibility	50 / 60 Hz
Output voltage regulation (line mode)	-17%, +8%
Output voltage regulation (Battery mode)	+/- 5%
Built-in UPS output receptacles	8 C13 outlet(s)
Included output power cables	Includes 2 C13 to C14 output power cables
Built-in controllable switched load banks	Three switchable two-outlet C13 load banks
Output AC waveform (AC mode)	Sine wave

Output AC waveform (battery mode)	Pure Sine wave
INPUT	
Rated input current (at maximum load)	6.52A
Nominal Input Voltage(s) Supported	230V AC
UPS input connection type	C14 inlet
UPS input connection description	IEC320-C14 input connection accepts a variety of detachable cordsets to match country or site-specific wall receptacles
Input circuit breaker	10A
BATTERY	
Full load runtime (minutes)	7 min. (1000w)
Half load runtime (minutes)	18 min. (500w)
Expandable battery runtime	Extended runtime supported via optional external battery packs
External battery pack compatibility	BP36V15-2U (limit 1); BP36V42-3U (multi-pack compatible)
DC system voltage (VDC)	36
Battery recharge rate (included batteries)	Less than 4.5 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC93-2U
Battery Access	Front panel battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 151 to 282
Overvoltage correction	Input voltages between 245 and 282 are reduced by 12%
Undervoltage correction	Input voltages between 181 and 199 are boosted by 12%
Severe undervoltage correction	Input voltages between 151 and 180 are boosted by 24%
LEDS ALARMS & SWITCHES	
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
Alarms	Audible alarm indicates power-failure, overload and low-battery conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	480

UPS AC suppression response time	Instantaneous
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	4 post 19 inch rackmount (mounting rail kit included)
Installation form factors supported with optional accessories	2 post rackmount (2POSTRMKITWM); Wallmount (2POSTRMKITWM); Tower (2-9USTAND); 2-4 post front rail rackmount (UPSHDEARKIT)
Primary form factor	Rackmount
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	3.5 x 17.5 x 13.5
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	8.9 x 44.4 x 34.3
Installed whole system total rack space height (rack spaces)	2U
Secondary form factor	Tower (requires 2-9USTAND)
Installed whole system dimensions in secondary form factor (height x width x depth / inches)	17.5 x 3.5 x 13.5
UPS dimensions in secondary form factor (height x width x depth / cm)	44.4 x 8.9 x 34.3
UPS / Power Module weight (lbs)	42.8
UPS / Power Module weight (kg)	19.4
UPS Shipping dimensions (height x width x depth / inches)	9 x 24 x 20.5
UPS Shipping dimensions (height x width x depth / cm)	22.9 x 61 x 52.1
Shipping weight (lbs)	50.5
Shipping weight (kg)	22.9
UPS housing material	Steel
Cooling method	Fan
Installed whole system dimensions in secondary form factor (height x width x depth / cm)	44.4 x 8.9 x 34.3
ENVIRONMENTAL	

Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	105.2
Battery mode BTU / hr. (full load)	463.6
COMMUNICATIONS	
Communications interface	USB; DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
Network monitoring port description	Supports detailed monitoring of UPS and site power conditions
PowerAlert software	Included
Communications cable	USB and DB9 cabling included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	2-4 milliseconds
Low voltage transfer to battery power (setpoint)	151
High voltage transfer to battery power (setpoint)	282
SPECIAL FEATURES	
Grounding lug	Back panel grounding lug
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Hot swappable batteries
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
CERTIFICATIONS	
UPS Certifications	Tested to CE (EU); Tested to GOST (Russia); Tested to SASO (Saudi Arabia); Tested to IRAM (Argentina)
WARRANTY	
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
---------------	-------------	------

BP36V15-2U	BP36V15-2U - External Battery Pack for UPS System	1
BP36V42-3U	BP36V42-3U - External Battery Pack for UPS System	1
DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	1
DNET1	Network Surge Suppressor - Essential protection for data and communication lines	1
DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	1
ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
PDU12IEC	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
SNMPWEBCARD	For remote monitoring and control via SNMP, Web, or Telnet.	1
U022-010	10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
WATCHDOGSW	WatchDog Service Monitoring / Reboot Software	1
2-9USTAND	Enables Tower Placement of Rackmount UPS Systems	1
2POSTRMKITWM	Enables 2-Post Rackmount or Wallmount Installation of Select Rackmount UPS Systems	1
MODBUSCARD	For remote monitoring and control via MODBUS protocol	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2687.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.