



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SPIKECUBE

### 1-outlet, Direct plug-in, 600 joule Surge Suppressor



#### Highlights

- 1 outlet / direct plug-in
- 600 joule rating
- Diagnostic LEDs
- \$5000 Ultimate Lifetime connected equipment (USA and Canada Only)

#### Description

The SPIKECUBE Surge Suppressor from Tripp Lite is a direct plug-in suppressor providing protection on one AC outlet. Its small size makes it ideal for protecting laptop computers, projectors and other portable electronics. A green "Protected" and red "Grounded" LED illuminates to indicate that adequate surge suppression is available. The unit has 600 joules of surge energy absorption. \$5,000 Ultimate Lifetime [connected equipment insurance](#) (USA and Canada Only).

#### Applications

- Ideal for laptop computers, video projectors, office machines, and appliances

#### Package Includes

- SPIKECUBE Surge Suppressor
- Warranty and instruction information

#### Features

- 1 outlet; direct plug-in
- Surge energy absorption: 600 joules; 6,500 amps
- Diagnostic LEDs indicate protection present (green) and ground present (red)
- \$5,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

#### Specifications

OVERVIEW	
Intended Application	Home/Office, Travel
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	1 NEMA 5-15R
INPUT	

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P input plug
Input cord length details	Direct Plug-In
Voltage compatibility (VAC)	120
Maximum Surge Amps	36000
<b>LEDS ALARMS &amp; SWITCHES</b>	
Diagnostic LEDs	Protected (green) & Grounded (red)
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	600
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	400, 500, 500
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping weight (lbs)	.150
Shipping weight (kg)	0.07
Unit Dimensions (HWD/in)	2.50 x 1.90 x 1.80
Unit Dimensions (HWD/cm)	6.35 x 4.83 x 4.57
Shipping Dimensions (HWD/in)	6.50 x 4.10 x 2.50
Shipping Dimensions (HWD/cm)	16.51 x 10.41 x 6.35
Unit weight (lbs)	.100
Unit weight (kg)	0.05
Material of construction	Plastic
Housing Color	Light Gray
Receptacle Color	Light Gray
AC line cord color	Light Gray
Style	Direct plug-in
Form factors supported	Direct plug in suppressor supports wall-mounting directly into AC receptacle

<b>SPECIAL FEATURES</b>	
<b>Appearance</b>	Ultra-compact portable direct plug-in protector in an attractive, grey lightweight enclosure
<b>CERTIFICATIONS</b>	
<b>UL1449 3rd Edition (AC Suppression)</b>	UL1449 3rd Edition
<b>Approvals</b>	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
<b>Product Warranty Period (Worldwide)</b>	Lifetime limited warranty
<b>Connected Equipment Insurance (U.S., Canada &amp; Puerto Rico)</b>	\$5,000 <a href="#">Ultimate Lifetime Insurance</a>

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=120](http://www.tripplite.com/en/products/model.cfm?txtModelID=120).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.