




Profibus I/O Modules with 16-Digital Inputs

0970 PSL 701



16 IN

Profibus-DP device with 16 digital inputs to connect standard sensors, combined M12 socket, rotary switches for addressing, M12 bus connection, 7/8" power supply.



Bit Assignment


Bit	7	6	5	4	3	2	1	0
M12 Input								
Byte 0	4B	4A	3B	3A	2B	2A	1B	1A
Byte 1	8B	8A	7B	7A	6B	6A	5B	5A

Diagnostic Indication

LED	Indication	Condition
1...8 A/B	yellow	channel status
1...8 A/DIA	red	periphery fault
Us	green	sensor/system power supply
BF	red	bus error
DIA	red	common indication for periphery faults

Pin Assignment

Bus connection M12	Power supply 7/8"	Input M12	
<p>1 = +5 V¹ 2 = Line A - GN 3 = GND (0 V)¹ 4 = Line B - RD 5 = earth housing = earth</p>	<p>1 = GND (0 V) 2 = GND (0 V) 3 = Earth 4 = +24 V 5 = -</p>	<p>1 = +24 V 2 = IN B 3 = GND (0 V) 4 = IN A 5 = Earth</p>	1 = internal signals: galvanically separated to sensors



Be Certain with Belden

Profibus I/O Modules with 16-Digital Inputs

0970 PSL 701

Technical Data

Environmental

Degree of protection IP 67
 Operating temperature range -10°C (+14°F) to +60°C (+140°F)

Mechanical

Weight 380 g
 Housing material PBT

Bus system

ID number 09CA hex
 GSD file Lum_09CA.GSD
 Transmission rate max. 12 MBaud
 Address range 1–125 dec
 Rotary address switches 1–99 dec
 Default address 99 dec

System/Sensors power supply

Rated voltage 24 V DC
 Voltage range 19–30 V DC
 Power consumption 120 mA
 Reverse polarity protection yes

Input power supply

Voltage range min. (U_{System} - 1.5 V)
 Sensor current 100 mA (at Tamb 30°C) per socket
 Short circuit-proof yes
 Indication LED green

Inputs

Rated input voltage 24 V DC
 Channel type N.O. p-switching
 Number of digital channels max. 16
 Channel status indicator LED yellow per channel
 Diagnostic indication LED red per channel

Diagnostic

Module diagnostic and single channel diagnostic according to Profibus specification (please see operating instructions under www.beldensolutions.com/downloads)

Included in delivery/accessories

Dust covers M12 2 pieces
 Attachable labels 10 pieces

Part Number

0970 PSL 701



The application of these products in harsh environments should always be checked before use. Specifications subject to alteration.