



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SU750XL

SmartOnline .75kVA On-Line Double-Conversion UPS, Tower, 100/110/120V NEMA outlets

Highlights



- 750VA / .75kVA / 600 watt on-line double-conversion tower UPS
- 100/110/120V +/-2% output at 50/60Hz, high efficiency economy mode option
- Expandable runtime, Hot-swappable battery modules
- USB, RS232 & EPO ports; support for SNMP/WEB card options
- Front panel status LEDs with detailed load and battery metering
- 2 independently switchable output load banks
- NEMA 5-15P input; 5-15R outlets

Description

The SU750XL on-line, double-conversion UPS protects critical server, networking or telecommunications equipment from blackouts, brownouts, voltage fluctuations and surges. Large-capacity 750VA/600W UPS continuously converts incoming AC to DC, then back to perfect sine wave AC output at 120V AC (+/-2%). Removes harmonic distortion, fast electrical impulses, frequency fluctuations and other hard-to-solve power problems not addressed by other UPS systems. True sine wave output and zero transfer time offer guaranteed compatibility with all equipment types. Includes 6 UPS supported outlets; 2 single-outlet load banks can be independently controlled via a software interface to selectively reboot remote equipment or shed less critical loads to extend battery runtime for the most critical equipment. Extended runtime available with optional BP24V15RT2U, BP24V28-2U, or BP24V70-3U external battery packs. Includes slot for internal SNMP/WEB card, plus DB9 enhanced serial monitoring port for unattended shutdown, remote control and monitoring of UPS system and power data. Includes USB and DB9 serial ports. Built-in DB9 port offers both enhanced RS-232 enabled monitoring data, plus contact closure monitoring ability. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Includes Tripp Lite's PowerAlert UPS power management software. Compatible with Tripp Lite's Watchdog service monitoring/rebooting software. Upright tower form factor; attractive all-black color scheme.

Package Includes

- SU750XL UPS System
- PowerAlert Software CD and cabling
- EPO (Emergency Power Off) cabling
- Owner's manual with warranty information

Features

- True on-line, double-conversion UPS provides constant, pure sine wave AC output
- Maintains continuous operation with zero transfer time through blackouts, brownouts, voltage fluctuations and surges
- Removes harmonic distortion, electrical impulses, frequency variations and other hard-to-solve power problems
- Accepts input voltages between 80-150V (65-150V at loads under 70%), regulating output to 120V AC +/-2%
- 750VA/600W output capacity with 6 x NEMA5-15R outlets
- Two built-in individually switchable load banks can be controlled via software interface to selectively reboot remote equipment or shed less critical loads to extend battery runtime for the most critical equipment (1 outlet per bank)
- Standard internal battery set provides 11 min. runtime at half load and 4 min. at full load
- Extended runtime available with optional BP24V15RT2U, BP24V28-2U, or BP24V70-3U external battery packs

- Some external battery configurations require the use of Tripp Lite's [External Battery Configuration Software](#) (see manual)
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- DB9 serial network interface supports RS-232 and contact closure messaging
- Slot for optional SNMP/WEB card (part# SNMPWEBCARD)
- Included PowerAlert UPS power management software and cabling provides monitoring of in-depth site power conditions, full UPS status and fault warnings, output load level and load bank power control
- Compatible with Tripp Lite's WatchDog service monitoring/rebooting software (part# WATCHDOGSW)
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Diagnostic LEDs
- Upright tower format; attractive all-black color scheme
- \$250,000 Ultimate Lifetime [connected equipment insurance](#) (USA and Canada Only)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	750
Output Watt Capacity (watts)	600
Output power factor	0.8
Crest Factor	3:1
Nominal Output Voltage(s) Supported	100V; 110V; 120V
Nominal Voltage details	120V default
Frequency compatibility	50 / 60 Hz
Frequency compatibility details	Output frequency matches input nominal on startup, defaults to 60 Hz on cold-start
Output voltage regulation (line mode)	+/- 2%
Output voltage regulation (Battery mode)	+/- 2%
Built-in UPS output receptacles	6 5-15R outlet(s)
Built-in controllable switched load banks	Two switchable single-outlet 5-15R load banks
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	Pure Sine wave
INPUT	
Rated input current (at maximum load)	6.2A
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 120V AC
UPS input connection type	5-15P
Input circuit breaker	15A

UPS Input cord length (ft.)	10
UPS Input cord length (m)	3
Recommended Electrical Service	15A 120V
BATTERY	
Full load runtime (minutes)	4 min. (600w)
Half load runtime (minutes)	11 min. (300w)
External battery pack compatibility	BP24V15RT2U (limit 1); BP24V28-2U (limit 1); BP24V70-3U (multi-pack compatible)
DC system voltage (VDC)	24
Battery recharge rate (included batteries)	Less than 6 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC24-SUTWR
Battery Access	Battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Online, double-conversion power conditioning
Overvoltage correction	2% output voltage regulation during overvoltages to 150
Undervoltage correction	2% output voltage regulation during undervoltages to 80
Severe undervoltage correction	2% output voltage regulation during undervoltages to 65 (under 70% load only)
LEDS ALARMS & SWITCHES	
LED Indicators	14 LEDs indicate line power, online mode, bypass mode, on-battery, overload, battery low, replace battery and fault status information - includes 4-LED meter display for load and battery charge level
Alarms	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	570
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC noise suppression	Yes

PHYSICAL	
Installation form factors supported with included accessories	Tower
Primary form factor	Tower
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	10 x 6.8 x 13.2
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	25.4 x 17.1 x 33.7
UPS / Power Module weight (lbs)	28.7
UPS / Power Module weight (kg)	13
UPS Shipping dimensions (height x width x depth / inches)	14.2 x 10 x 18.5
UPS Shipping dimensions (height x width x depth / cm)	36.2 x 25.4 x 47
Shipping weight (lbs)	34.2
Shipping weight (kg)	15.5
UPS housing material	Steel
Cooling method	Fan
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	304.8
Battery mode BTU / hr. (full load)	304.8
Audible Noise	< 45 dB at front side 1m
COMMUNICATIONS	
Communications interface	USB (HID enabled); DB9 Serial; Contact closure; EPO (emergency power off); Slot for SNMP/Web interface
Network monitoring port description	Supports detailed monitoring of UPS and site power conditions; DB9 port supports RS232 and contact closure communications
PowerAlert software	Included
Communications cable	USB and DB9 cabling included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications

LINE / BATTERY TRANSFER	
Transfer time	No transfer time (0 ms.) in online, double-conversion mode
Low voltage transfer to battery power (setpoint)	80V (100% load), 65V (
High voltage transfer to battery power (setpoint)	150
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Automatic inverter bypass; Hot swappable batteries
Green & high efficiency features	Individually controllable load banks
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Meets FCC Part 15 Category B (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Related Model	Description	Qty.
SNMPWEBCARD	For remote monitoring and control via SNMP, Web, or Telnet.	1
ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
RELAYIOCARD	Programmable Relay I/O Card	1
MODBUSCARD	For remote monitoring and control via MODBUS protocol	1
AS400CABLEKIT2	Power Management Tools - UPS Communication Cable Kit for System i / AS400 / iSeries Servers	1
BP24V15RT2U	BP24V15RT2U - External Battery Pack for UPS System	1
BP24V28-2U	BP24V28-2U - External Battery Pack for UPS System	1
BP24V70-3U	BP24V70-3U - External Battery Pack for UPS System	1
WEXT3-500-1500	3-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 1500VA or less	1
WEXT5-500-1500	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 1500VA or less	1
PDU1215	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
PDUB15	Dual source Power Distribution Unit / PDU with Manual Transfer Switch enables Hot-swappable UPS Replacement in Critical Network Applications	1
PDUV15	Safe, reliable power distribution for critical networking equipment	1

PDUNV	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
PDUMH15	Metered PDU / Power Distribution Unit - Safe, reliable power distribution with digital current meter	1
PDUMV15	Metered PDU / Power Distribution Unit - Safe, reliable power distribution with digital current meter	1
PDUMH15AT	Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching	1
PDUMNH15	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1
PDUMNV15	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1
PDUMH15ATNET	Switched, Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching, individual outlet control and remote network interface	1
PDUMV15NET	Switched, Metered PDU with Remote Monitoring - 0U Vertical Rackmount Power Distribution Unit for Networks with Individually Switchable Outlets, Current Metering, Remote Monitoring and Control	1
P007-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P007-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P007-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P010-012	12-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P022-001	1-ft. 18AWG Power Extension cord (NEMA 5-15R to NEMA 5-15P)	1
P023-001	1-ft. 14AWG Power Adapter cord (NEMA L5-15R to NEMA 5-15P)	1
P034-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-15P)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3299.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.