



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TE1200

TE Series 1200VA Tower Line-Interactive 120V UPS with serial port



Highlights

- 6 outlets
- Automatic Voltage Regulation (AVR) corrects brownouts and overvoltages
- Larger scale battery produces significantly longer runtimes
- Serial port works with software to facilitate unattended shutdown
- \$200,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's TE1200 UPS System provides line-interactive voltage regulation and long lasting battery support for mid-size business telephone systems, voicemail systems, personal computers and other communications, network and telecom applications. 1200VA power handling capacity and large capacity battery system maintains continuous operation through power interruptions with over 2 hours runtime for many phone systems and over 1 hour for larger systems. Line interactive voltage regulation maintains normal 120 volt output levels during brownouts as low as 75V and overvoltages as high as 147V, saving battery reserves for use only during complete power failures. Includes 6 outlets, diagnostic LEDs and a built-in serial port that works with Free PowerAlert Software and cabling to provide automatic unattended shutdown of network and PC applications. \$200,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only).

Package Includes

- TE1200 UPS System
- Warranty information
- Instruction manual

Features

- Provides connected equipment with continuous power during short and long duration loss of commercial power
- Line-interactive voltage regulation corrects brownouts and overvoltages from 75 to 147 volts back to usable 120V output levels, without using battery power
- Supports loads up to 1200VA/940 watts
- 16 minutes half load runtime (600VA/470 watts), 7 minutes full load runtime (1200VA/940 watts)
- 6 protected outlets; 6-ft. cord
- DB9 network interface
- Complete surge protection and EMI/RFI noise filtering
- \$200,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only)
- 5 diagnostic LEDs indicate AC present, on battery, voltage correction, overload & battery low/replace
- Battery replacement door

Specifications

OUTPUT

Output Volt Amp Capacity (VA)	1200
Output kVA capacity (kVA)	1.2
Output Watt Capacity (watts)	940
Nominal Output Voltage(s) Supported	115V; 120V
Frequency compatibility	60 Hz
Output voltage regulation (line mode)	-18%, +8%
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	6 5-15R outlet(s)
Basic PDU options	PDU1215 (1U / 13 5-15R outlets); PDUNV (1U / 2 C19, 12 C13 outlets); PDU1415 (0U / 14 5-15R outlets); PDUV15 (0U / 12 5-15R outlets)
Metered PDU options	PDUMH15 (1U / 13 5-15R outlets); PDUMH15AT (1U / 8 5-15R outlets)*; PDUMV15 (0U / 16 5-15R outlets)
Switched PDU options	PDUMH15ATNET (1U / 8 5-15R outlets)*; PDUMV15NET (0U / 16 5-15R outlets)
External PDU redundancy options	*Auto Transfer Switch features utilizing the secondary PDU input cord are compatible with Smart Online UPS models only
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	8.25A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
BATTERY	
Full load runtime (minutes)	7 min. (940w)
Half load runtime (minutes)	16 min. (470w)
DC system voltage (VDC)	36
Battery recharge rate (included batteries)	Less than 8 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC53

Battery Access	Battery access door
VOLTAGE REGULATION	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147
Overvoltage correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage correction	Input voltages between 93 and 107 are boosted by 14%
Severe undervoltage correction	Input voltages between 75 and 92 are boosted by 30%
LEDS ALARMS & SWITCHES	
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
Alarms	Audible alarm indicates power-failure and low-battery conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	480
UPS AC suppression response time	Instantaneous
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower
Installation form factors supported with optional accessories	Wallmount (UPSWM - tower mounting kit)
Primary form factor	Tower
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	12.8 x 7.5 x 9.2
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	32.4 x 19 x 23.5
UPS / Power Module weight (lbs)	38
UPS / Power Module weight (kg)	17.3
UPS Shipping dimensions (height x width x depth / inches)	18.2 x 12 x 13.8
UPS Shipping dimensions (height x width x depth / cm)	46.4 x 30.5 x 34.9
Shipping weight (lbs)	42

Shipping weight (kg)	19.1
UPS housing material	PVC
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	204
Battery mode BTU / hr. (full load)	277.9
COMMUNICATIONS	
Communications interface	DB9 Serial; Contact closure
PowerAlert software	Free download from www.tripplite.com
Communications cable	DB9 cable included
LINE / BATTERY TRANSFER	
Transfer time	2-4 milliseconds
Low voltage transfer to battery power (setpoint)	75
High voltage transfer to battery power (setpoint)	147
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Related Model	Description	Qty.
CT120	Instant-Read- AC Outlet Circuit Tester	1
DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	1
DNET1	Network Surge Suppressor - Essential protection for data and communication lines	1
DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	1

UPSWM	Wallmount Bracket and installation accessories (4 washers, 4 screws, 1 Velcro safety strap)	1
WEXT3-OMNI	3-Year Extended Warranty - For OmniSmart, OmniPro, OmniVS	1
WEXT5-OMNI	5-Year Extended Warranty - For OmniSmart, OmniPro, OmniVS	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=65.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.