



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLP1008TELTV

10 outlet, 8-ft cord, 3345 joules, Tel/Modem and Coaxial protection - Protect It! Surge Suppressor



Highlights

- 10 outlets / 8-ft. cord
- 1 in/2 out tel/modem surge protection
- 1 line 2.2GHz gold coaxial protection
- 3345 joule rating
- \$150,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

Description

Tripp Lite's TLP1008TELTV offers economical AC surge suppression for protection of workstations, PCs, telecom systems, home electronics and other sensitive equipment. The TLP1008TELTV features 10 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs to warn of suppressor damage. The unit has a surge suppression rating of 3345 joules to shield equipment from line noise and the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. Built-in 2.2GHz goldcoax jacks prevent surges from damaging your cable/satellite equipment. \$150,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

PLUG/OUTLETS: Input: NEMA5-15P/Output: 10 NEMA5-15R/8-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 5 transformer-spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/3345 joules/400V UL1449 3rd Edition

Applications

- Ideal for protecting TVs, DVDs, satellites, stereos and other entertainment systems

Package Includes

- TLP1008TELTV surge suppressor
- 6-ft. RJ11 cable
- 6-ft gold coax cable
- Instruction manual and warranty information

Features

- 10 outlets with child safety covers
- 8-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment; - built-in splitter protects two devices sharing a single line; 6-ft. telephone cord included
- Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment; 6-ft gold coax cable included
- Surge suppression rating: 3345 joule protection
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate up to 4 transformers without blocking remaining outlets
- Keyhole supports for wall mounting
- \$150,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only) covers connected equipment
- Failsafe shutdown mode

- Lighted power switch

Specifications

OVERVIEW	
Intended Application	Home/Office, Audio/Video
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Overload protection	15A resettable circuit breaker
Outlet quantity / type	10 NEMA 5-15R
Transformer accommodation	Supports 4 large transformer plug accessories without covering remaining outlets, accepts up to 8 transformers total
Outlet safety covers	Includes built-in sliding outlet safety covers
Outlet orientation	Two rows of outlets, including 4 widely spaced for transformers
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	8
Input cord length (m)	2.4
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	135000
LEDS ALARMS & SWITCHES	
Switches	Two-position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	3345
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150V
UL1449 let through rating	400V - UL Verified
EMI / RFI filtering	Up to 40dB
DATALINE SURGE SUPPRESSION	

Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (HWD/in)	11.6 x 5 x 2.25
Unit Dimensions (HWD/cm)	29.5 x 12.7 x 6.5
Shipping Dimensions (HWD/in)	14.75 x 7.75 x 2.3
Shipping Dimensions (HWD/cm)	37.5 x 19.7 x 5.8
Unit weight (lbs)	2.2
Unit weight (kg)	1.0
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Black
Receptacle Color	Black
AC line cord color	Black
Style	Strip
Outlets center to center measurement	Between Standard Outlets = 28.4mm; Between Standard and Transformer Outlets = 56.8mm
Keyhole slot center to center measurement	108mm
SPECIAL FEATURES	
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications

WARRANTY**Product Warranty Period
(Worldwide)**

Lifetime limited warranty

**Connected Equipment
Insurance (U.S., Canada &
Puerto Rico)**\$150,000 [Ultimate Lifetime Insurance](#)

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.triplite.com/en/products/model.cfm?txtModelID=2635.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.