

## M23 Field Attachable Connectors


RSC-F-120/13.5 | RSC 190/9



### Male, 12-Pole

Field attachable connector, M23 male connector 12-pole with threaded joint, external thread, assembling with solder connections.


RSC-F-120/13.5



### Male, 19-Pole

Field attachable connector, M23 male connector, 19-pole with threaded joint, assembling with solder connections.

RSC 190/9



## Pin Assignments

### M23 - Male

#### 12 poles



#### 19 poles





## Be Certain with Belden

### M23 Field Attachable Connectors

RSC-F-120/13.5 | RSC 190/9

#### Technical Data

##### Environmental



Degree of protection	RSC-F-120/13.5: IP 67 RSC 190/9: IP 65
Operating temperature range	RSC-F-120/13.5: -40°C (-40°F) / +90°C (+194°F) RSC 190/9: -25°C (-13°F) / +110°C (+230°F)

##### Mechanical

Housing / Molded body	CuZn, nickel-plated
Insert	RSC-F-120/13,5: PBT GF RSC 190/9: PA
Contact	CuZn, pre-nickel and gold-plated
Receptacle shell	CuZn, nickel-plated
O-ring	FKM (only RSC-F-120/13,5)
Mode of connection	solder connection
Connectable conductor	max. 1.0 mm <sup>2</sup>

##### Electrical

Contact resistance	RSC-F-120/13,5: $\leq 5 \text{ m}\Omega$ RSC 190/9: $\leq 3 \text{ m}\Omega$
Nominal current at 40°C	RSC-F-120/13,5: 8 A RSC 190/9: 16 x 8 A / 3 x 10 A
Nominal voltage	150 V
Test voltage	1.5 kV eff. / 60 s
Insulation resistance	$> 10^9 \Omega$
Pollution degree	3

Part Number	Pins	Cable Diameter Range	Characteristics
<b>Male</b>	<b>Male</b>		
RSC-F-120/13.5	12	Ø 10.0 – 14.0 mm	 
	RSC 190/9	19	Ø 6.0 – 10.0 mm 